

Product data sheet

Specifications

SQUARE D



Foot Switch, Harmony 9002AW, industrial, pedal and side shields, DPDT contact, NEMA 2, 4, 13 enclosure, 0.6A at 600V AC

9002AW14

Product availability: Stock - Normally stocked in distribution facility

Main

| | |
|-------------------------|---|
| Range | 9002AW |
| Product | Foot switch |
| Contact Operation | 1 step |
| Certifications | UL Listed CSA |
| Cable Entry | 0.75 inch NPT conduit entrance |
| Contact Arrangement | DPDT |
| Enclosure Rating | NEMA 2/4/13 |
| Voltage Rating | 600 V AC/DC |
| Protection | Side shield Pedal shield |
| Operator Action | Spring return |
| Rated Breaking Capacity | 3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 0.75 A 480 V AC inductive control circuit UL 508 0.6 A 600 V AC inductive control circuit UL 508 3 A 120 V AC resistive control circuit UL 508 0.2 A 125 V DC resistive control circuit UL 508 |
| Height | 4.8 in (123 mm) |
| Width | 5.4 in (137 mm) |
| Depth | 9.02 in (229 mm) |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10CS121441 |
| Discount Schedule | 0CS1 |
| GTIN | 785901817413 |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------|---------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 5.70 in (14.478 cm) |
| Package 1 Width | 5.70 in (14.478 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

| | |
|---------------------|-------------------------|
| Package 1 Length | 12.10 in (30.734 cm) |
| Package weight(Lbs) | 4.559 lb(US) (2.068 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)

15

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Circularity Profile

No need of specific recycling operations

Take-back

No

WEEE Label

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



