

Product data sheet

Specifications

Linergy FT, Comb busbar, 63A, 2 tap-offs, 54mm pitch



GV2G254

Main

Range	Linergy
Product name	FT
Device short name	GV2G
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys GV2 TeSys K TeSys U TeSys Deca
Number of tap-offs	2
[I _{th}] conventional free air thermal current	63 A
Connection pitch	54 mm

Complementary

Fixing mode	Terminals:
[U _i] rated insulation voltage	690 V
Length	98 mm
Product weight	0.038 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	8.000 cm
Package 1 Length	14.000 cm
Package 1 Weight	40.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	80
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.360 kg

Unit Type of Package 3	P06
Number of Units in Package 3	2560
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	118.100 kg

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant**

Use Again

Repack and remanufacture


End of life manual availability [End of Life Information](#)

Take-back **No**


WEEE Label  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Sets of Busbars GV2G... with Terminal Block GV1G09



Sets of Busbars GV2G245, GV2G254, GV2GR272



	I
GV2G245 (2 x 45 mm)	89
GV2G254 (2 x 54 mm)	98
GV2G272 (2 x 72 mm)	116