

# Product data sheet

## Characteristics

# AR3100SP

APC NetShelter SX, Server Rack Enclosure,  
42U, Shock Packaging, 2000 lbs, Black, 1991H  
x 600W x 1070D mm



### Overview

#### Presentation

NetShelter SX cabinet and packaging system designed to safely integrate, transport, unload and deploy up to 2000 lbs (907 kg) of IT equipment. The cabinet is paired with a shock absorbing pallet, unloading ramp, and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).

#### Lead time

Usually in Stock

### Main

Number of rack unit	42U
Provided equipment	Baying hardware Documentation CD Key(S) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels

### Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	23.62 in (60 cm)
Depth	42.13 in (107 cm)
Net Weight	275.78 lb(US) (125.09 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	36.02 in (91.49 cm)
Minimum Mounting Depth	7.52 in (19.1 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3750 lb(US) (1700.97 kg) static

### Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

## Ordering and shipping details

GTIN	731304309857
Package weight(Lbs)	534.00 lb(US) (242.22 kg)

## Packing Units

Package 1 Height	85.79 in (217.9 cm)
Package 1 width	43.50 in (110.5 cm)
Package 1 Length	52.01 in (132.1 cm)
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------