

Product data sheet

Characteristics

AR3140

APC NetShelter SX, Networking Rack Enclosure, 42U, Black, 1991H x 750W x 1070D mm with Casters, Feet, Vertical Cable Managers, Side Panels



Overview

Presentation	NetShelter SX Networking Enclosure expands Schneider Electric's superior IT enclosure line with improved support for high density networking applications. Integrated high density cable managers and improved cable access roof provide support for large cable bundles. When combined with the Side Airflow Duct Kit, the Networking Enclosure ensures complete isolation of cold intake and hot exhaust air for large switches and SAN directors.
Lead time	Usually in Stock

Main

Product or Component Type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Key(S) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels Vertical cable managers

Physical

Height	78.39 in (199.1 cm)
Width	29.53 in (75 cm)
Depth	42.13 in (107 cm)
Net Weight	343.81 lb(US) (155.95 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Mounting Location	Front Rear
Maximum Mounting Depth	32.25 in (81.92 cm)
Minimum Mounting Depth	11.00 in (27.94 cm)
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3750 lb(US) (1700.97 kg) static

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	731304275572
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	83.39 in (211.8 cm)
Package 1 Width	33.50 in (85.09 cm)
Package 1 Length	45.51 in (115.6 cm)
Package 1 Weight	370.77 lb(US) (168.18 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------