

# Product data sheet

Specifications



Head for non illuminated push button, Harmony XB6, blue rectangular pushbutton Ø 16 spring return unmarked

ZB6DA6

## Main

|                               |                                      |
|-------------------------------|--------------------------------------|
| Range of product              | Harmony XB6                          |
| Product or component type     | Head for non-illuminated push-button |
| Device short name             | ZB6                                  |
| Bezel material                | Plastic                              |
| Mounting diameter             | 16 mm                                |
| Sale per indivisible quantity | 1                                    |
| Shape of signaling unit head  | Rectangular                          |
| Type of operator              | spring return                        |
| Operator profile              | Blue flush, unmarked                 |

## Complementary

|                    |          |
|--------------------|----------|
| CAD overall width  | 24 mm    |
| CAD overall height | 18 mm    |
| CAD overall depth  | 33 mm    |
| Product weight     | 0.016 kg |

## Environment

|                                       |                                                                                                                                                                                                                    |
|---------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TC                                                                                                                                                                                                                 |
| Ambient air temperature for storage   | -40...70 °C                                                                                                                                                                                                        |
| Ambient air temperature for operation | -25...70 °C                                                                                                                                                                                                        |
| Electrical shock protection class     | Class II conforming to IEC 61140                                                                                                                                                                                   |
| IP degree of protection               | IP65 conforming to IEC 60529                                                                                                                                                                                       |
| NEMA degree of protection             | NEMA 13 conforming to UL 50<br>NEMA 4 conforming to UL 50<br>NEMA 4X conforming to UL 50<br>NEMA 13 conforming to CSA C22.2 No 94<br>NEMA 4 conforming to CSA C22.2 No 94<br>NEMA 4X conforming to CSA C22.2 No 94 |
| Standards                             | EN/IEC 60947-5-1<br>JIS C8201-5-1<br>CSA C22.2 No 14<br>EN/IEC 60947-1<br>UL 508<br>JIS C 852<br>EN/IEC 60947-5-5<br>JIS C8201-1                                                                                   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                        |                                                                                                                                                                                |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product certifications | CCC<br>GOST<br>CSA<br>UL                                                                                                                                                       |
| Vibration resistance   | +/- 3 mm (f= 2...500 Hz) conforming to IEC 60068-2-6<br>5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6                                                                       |
| Shock resistance       | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 3.0 cm  |
| Package 1 Width              | 3.0 cm  |
| Package 1 Length             | 5.0 cm  |
| Package 1 Weight             | 9.0 g   |
| Unit Type of Package 2       | S01     |
| Number of Units in Package 2 | 60      |
| Package 2 Height             | 15.0 cm |
| Package 2 Width              | 15.0 cm |
| Package 2 Length             | 40.0 cm |
| Package 2 Weight             | 765.0 g |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

| Environmental footprint          |                                               |
|----------------------------------|-----------------------------------------------|
| Total lifecycle Carbon footprint | 1                                             |
| Environmental Disclosure         | <a href="#">Product Environmental Profile</a> |

Use Better

| Materials and Substances               |                                                                                                                                                                                                                                                                                       |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard | Yes                                                                                                                                                                                                                                                                                   |
| Packaging without single use plastic   | No                                                                                                                                                                                                                                                                                    |
| <a href="#">EU RoHS Directive</a>      | Pro-active compliance (Product out of EU RoHS legal scope)                                                                                                                                                                                                                            |
| California proposition 65              | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |


Use Again

| Repack and remanufacture        |                                         |
|---------------------------------|-----------------------------------------|
| End of life manual availability | <a href="#">End of Life Information</a> |
| Take-back                       | No                                      |

Dimensions Drawings

Rectangular Head for Illuminated or Non Illuminated Pushbutton

Dimensions




Mounting and Clearance

Panel Cut-out


---

For Rectangular Head




Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection

Front Panel Cut-out (Viewed from Installer's Side)



Printed Circuit Board Drillings (Viewed from Electrical Block Side)



**A** 24 mm/0.94 in. minimum for rectangular heads, 18 mm/0.71 in. minimum for square or circular heads

**B** 18 mm/0.71 in. minimum

(1) 6 x Ø 1.1 mm / 6 x Ø 0.04 in. holes.

(2) 1 x Ø 2.6<sup>0</sup><sub>-0,2</sub> mm / 1 x Ø 0.10<sup>0</sup><sub>-0,008</sub> in. hole for locating pin, only when using socket adaptor ZB6Y010.

(3) 1 x Ø 3.2<sup>0</sup><sub>-0,2</sub> mm / 1 x Ø 0.13<sup>0</sup><sub>-0,008</sub> in. hole for fixing of printed circuit board onto the front panel using body bracket ZB6Y011. This hole must be drilled on the left-hand side, when heads are positioned at the normal angle. Fit a body bracket ZB6Y011 every 72 mm/2.83 in. maximum for cut-outs on 24 mm/0.94 in. centres (rectangular heads) and 54 mm/2.13 in. maximum for cut-outs on 18 mm/0.71 in. centres (square or circular heads).


**General tolerances of the panel and printed circuit board:** T1, T2: T1 + T2 = 0.3 mm/0.01 in. maximum.

**Installation precautions:**

Thickness of printed circuit board: 1.6 mm/0.06 in. minimum.


Mounting with Body Bracket

With socket adaptor ZB6Y010



- (1) Head
- (2) Nut
- (3) Body
- (4) Body bracket
- (5) Contact block
- (6) Socket adaptor
- (7) Panel
- (8) Printed circuit

Direct mounting without socket adaptor ZB6Y010



- (1) Head
- (2) Nut
- (3) Body
- (4) Body bracket
- (5) Contact block
- (6) Panel
- (7) Printed circuit

Technical Illustration

Dimensions

