



Overview

Presentation	The Step-Down Transformer converts high voltage (208 or 200 VAC) output into low voltage (120 or 100 VAC) output for powering low voltage AC equipment.
Lead time	Usually in Stock

General

Provided Equipment	Documentation CD Hardwire panel Installation guide Rack Mounting brackets User Manual Mounting Hardware
--------------------	--

Physical

Color	Black
Depth	29.49 in (74.9 cm)
Height	6.89 in (17.5 cm)
Product Weight	220.46 lb(US) (100 kg)
Width	17.01 in (43.2 cm)

Input

Max line current	60 A
Input current limits	60 A
Load Capacity	10000 VA
Input Frequency	45...65 Hz
Number of input connectors	1 Hard Wire 3-wire (2PH + G) 1 Hard Wire 3-wire (1PH+N+G)
Nominal Input Voltage	208 V 230 V 240 V

Output

Max current draw	60 A
Number of power socket outlets	0
Efficiency	95 %
Output connector type	Hard Wire 3-wire (H N + E) 1 Hard Wire 3-wire (2PH + G) 1
Output voltage	120 V 208 V 230 V 240 V

Conformance

Product Certifications	CSA UL Listed
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304242208
Package weight(Lbs)	275.58 lb(US) (125 kg)

Packing Units

Package 1 Height	15.98 in (40.6 cm)
Package 1 width	23.62 in (60 cm)
Package 1 Length	39.37 in (100 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------