

GUPXCB150CD300

GUTOR PXC UL Battery Cabinet, 150A Breaker, 300 Watt/Cell Battery



Overview

Presentation	Fully populated, VRLA battery cabinets. Includes all breakers and fuses, line up and match capability, top and/or bottom cable entry.
Lead time	Special Order - Call for Quoted Lead Times

Main

Battery Type	VRLA
--------------	------

Physical

Height	82.72 in (210.1 cm)
Width	39.69 in (100.8 cm)
Depth	31.50 in (80 cm)
Net Weight	2550.00 lb(US) (1156.66 kg)
Mounting Mode	Not rack-mountable

Conformance

Standards	FCC Part 15 class A UL 1778
-----------	--------------------------------

Environmental

Ambient Air Temperature for Operation	14...104 °F (-10...40 °C)
Operating altitude	0...9842 ft
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage altitude	0...16404 ft (0.00...4999.94 m)
Storage Relative Humidity	0...95 % Non-condensing

Batteries & Runtime

Battery Placement	Battery Cabinet
Battery Slots Empty	0
Included Battery Modules	0
Battery manufacturer	C&D and EnerSys
Device mounting	Enclosed battery cabinet
Battery Volt-Amp-Hour Capacity	0 VAh

Ordering and shipping details

Nbr. of units in pkg.	1
Package weight(Lbs)	2644.45 lb(US) (1199.5 kg)

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	90.71 in (230.4 cm)
Package 1 width	54.02 in (137.2 cm)
Package 1 Length	38.50 in (97.8 cm)
Number of Units in Package 3	1

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------