

Product data sheet

Specifications



Disconnect switch, TeSys VLS, body switch, 30A, 20HP at 480VAC, UL98, three phase, 100kA SCCR, size 2, door mount

VLS3P030D2

Product availability: Stock - Normally stocked in distribution facility

Main

Range	TeSys
Product Name	TeSys VARIO LS
Device Short Name	VLS3P
Product Type	Switch body

Complementary

Mounting Support	Door
Performance Level	High performance
Number of Poles	3P
Contact Type and Composition	3 NO
Color	Gray
[Ue] UL Rated Operational Voltage	600 V AC 50/60 Hz UL 508
Network type	AC
Network frequency	50/60 Hz
UL Maximum Horsepower Ratings	10 hp 200/208 V AC 10 hp 240 V AC 20 hp 480 V AC 30 hp 600 V AC 2 hp 120 V AC 5 hp 240 V AC
[Ue] IEC Rated Operational Voltage	690 V AC 50/60 Hz
IEC Rated Operational Power in W	15 kW 400 V AC-23A) 15 kW 500 V AC-23A) 30 kW 690 V AC-23A)
[Ie] Rated Operational Current	30 A Ue: 600 V UL98 30 A AC-21A Ue: 400 V 30 A AC-21A Ue: 500 V 30 A AC-21A Ue: 690 V 30 A AC-22A Ue: 400 V 30 A AC-22A Ue: 500 V 30 A AC-22A Ue: 690 V 30 A AC-23A Ue: 400 V 30 A AC-23A Ue: 500 V 30 A AC-23A Ue: 690 V
[Ith] Conventional Free Air Thermal Current	30 A (at 131 °F (55 °C))
[Ithe] Conventional Enclosed Thermal Current	30 A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Making capacity (I Rms)	630 A 690 V AC-23A 94.5 A 690 V AC-21A 189 A 690 V AC-22A
Breaking Capacity	94.5 A 690 V AC-21A) 189 A 690 V AC-22A) 504 A 690 V AC-23A)
SCCR	Circuit-breaker 100 A maximum: 100 kA at 480 V AC Fuse CC 100 A maximum: 100 kA at 480 V AC Fuse J 100 A maximum: 100 kA at 480 V AC Fuse T 100 A maximum: 100 kA at 480 V AC Fuse CC 60 A maximum: 50 kA at 600 V AC Fuse J 60 A maximum: 50 kA at 600 V AC Fuse T 60 A maximum: 50 kA at 600 V AC
Rated Conditional Short Circuit Current	50 kA 400 V 63 A gG
[Icm] Rated Short Circuit Making Capacity	3550 A 690 V
Intermittent duty class	Class 120 - 60 %
[Uiimp] rated impulse withstand voltage	8 kV
[Icw] rated short-time withstand Rms current	2500 A 690 V 1 s
Mechanical Durability	30000 cycles
Electrical Durability	30000 cycles AC-21
UL Wire Size	AWG 12...AWG 1 copper
IEC Terminal Connection	Power circuit screw clamp terminals 0.08 in ² (50 mm ²) solid Power circuit screw clamp terminals 0.1 in ² (70 mm ²) flexible - without cable end
Tightening Torque	Power circuit 44.3...53.1 lbf.in (5...6 N.m) screw clamp terminals
Height	2.8 in (70 mm)
Width	2.8 in (70 mm)
Depth	3.9 in (100 mm)
Product Weight	0.805 lb(US) (0.365 kg)

Environment

Standards	UL98 CSA C22.2 No 4 IEC 60947-3
Product Certifications	cULus GL
Degree of Protection	IP20 conforming to IEC 60529
Mechanical Robustness	Vibrations 2...100 Hz Fc 0.7 g) IEC 60068-2-6 Shocks 11 ms Ea 15 gn) IEC 60068-2-27
Ambient Air Temperature for Operation	-13...131 °F (-25...55 °C)
Fire Resistance	1760 °F (960 °C) IEC 60695-2-11

Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481385963
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.15 in (8.000 cm)
Package 1 Width	3.35 in (8.500 cm)
Package 1 Length	4.72 in (12.000 cm)
Package weight(Lbs)	15.309 oz (434.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	26.870 lb(US) (12.188 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant

Use Again


Repack and remanufacture

Take-back	No
-----------	----

Technical Illustration

Dimensions

VLS3P030D2
VLS3P030D2
VLS3P080D2
VLS3P100D2
VLS3P125D2



ALL DIMENSIONS ARE APPROXIMATE.
REFER TO TECHNICAL DRAWINGS AND DOCUMENTATION FOR COMPLETE INFORMATION.