

Product data sheet

Specifications



single phase relay, Harmony Solid State Modular Relays, 25A, DIN rail mount, zero voltage switching, input 4 to 32V DC, output 48 to 600V AC

SSM3A325BD

Main

Range of product	Harmony Solid State Relays
Device short name	SSM3
Product or component type	Modular DIN rail relay
Number of channels	3
Number of phases	3 phases
Output switching mode	Zero voltage switching

Complementary

Mounting support	Symmetrical DIN rail
[In] rated current	25 A
Output voltage	48...600 V AC
[Uc] control circuit voltage	4...32 V DC
Tightening torque	0.6...0.7 N.m for input 1.36...1.7 N.m for output
Connections - terminals	Screw terminals: 0.2...1.3 mm ² , (AWG 24...AWG 16) for input Screw terminals: 1.3...5.3 mm ² , (AWG 16...AWG 10) for output
maximum capacitance	8 pF for input/output
Insulation resistance	1000 MΩ
Local signalling	LED (green) for input status
Switching voltage	4 V DC turn-on 1 V DC turn-off
input current	22...28 mA
Solid state output type	Zero voltage switching
Load current	0.1...25 A
transient overvoltage	1100 V
Surge current	286 A for 20 ms at 50 Hz 300 A for 16.6 ms at 60 Hz
Maximum voltage drop	<1.35 V on-state
Motor power hp	1 hp 40 °C 240 V AC 2 hp 40 °C 380 V AC 3 hp 40 °C 480 V AC
Maximum I ² t for fusing	410 A ² .s for 10 ms at 50 Hz 374 A ² .s for 8.3 ms at 60 Hz
Maximum leakage current	0.25 mA off-state
DV/dt	500 V/μs off-state at maximum voltage

Response time	0.5 cycle (turn-on) 0.5 cycle (turn-off)
power factor	0.5 (with maximum load)
Overvoltage category	III
Width	90 mm
test button	Without test button
Product weight	0.74 kg

Environment

Dielectric strength	4 kV AC for input/output 4 kV AC for input or output to case
Pollution degree	2
Standards	CSA C22.2 No 14 IEC 60950-1 UL 508
Product certifications	CSA UL EAC
Marking	EAC CSA UL CE
IP degree of protection	IP20
Ambient air temperature for operation	-20...80 °C
Ambient air temperature for storage	-40...100 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.000 cm
Package 1 Width	11.000 cm
Package 1 Length	11.000 cm
Package 1 Weight	764.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	5
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.278 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	304
----------------------------------	-----

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	134201bc-d293-4667-9cca-10a7f11729e0
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

Repack and remanufacture

Take-back	No
-----------	----


Dimensions Drawings

Dimensions



- (1) Side view
- (2) Top view
- (3) Front view
- (A) Mounting hole
- (B) Mounting hole / slot

Performance Curves

Derating Curves

A : Output Current (Amps)

B : Ambient Temperature (°C)

Technical Illustration

Dimensions




Image of product / Alternate images

Alternative

