

Product data sheet

Specifications



Disconnect switch, Tesys VLS, set of 2 terminal covers, for 3 pole unit terminals, 16A to 40A devices

VLSC3P1

Product availability: Stock - Normally stocked in distribution facility

Main

Range	TeSys
Device short name	VLSC
Product or Component Type	Terminal cover
Accessory / separate part category	Protection accessory
Range compatibility	TeSys TeSys VARIO LS VLS3P
Poles description	3P
Quantity per Set	Set of 2

Complementary

Fixing Mode	Clipped
Height	1.04 in (26.4 mm)
Width	1.4 in (36 mm)
Depth	1.8 in (46 mm)
Net Weight	0.040 lb(US) (0.018 kg)

Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481157126
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.10 in (2.800 cm)
Package 1 Width	2.36 in (6.000 cm)
Package 1 Length	2.36 in (6.000 cm)
Package weight(Lbs)	0.635 oz (18.000 g)
Unit Type of Package 2	S01
Number of Units in Package 2	40
Package 2 Height	5.91 in (15.000 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	32.240 oz (914.000 g)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

Use Again

 Repack and remanufacture	
Take-back	No