

Product data sheet

Specifications



Wall mounted polyester enclosure,
PanelSeT PLM, plain door,
308x255x160mm, IP66, IK10, RAL
7035

NSYPLM3025G

Product availability: Stock - Normally stocked in distribution facility

Main

Range	PanelSeT
Device short name	PLM
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	12.1 in (308 mm)
Nominal width	10.04 in (255 mm)
Nominal depth	6.3 in (160 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 door 1 lock
Door type	Solid
Lock type	3 mm double-bar lock

Complementary

Number of locks	1
Mounting plate description	Without mounting plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	polyester reinforced with fibreglass
color	Gray RAL 7035)
Standards	IEC 62208 NEMA classification 13 NEMA classification 4X
Product Certifications	UL
Electrical Insulation Class	Class II

Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature for Operation	-40...176 °F (-40...80 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
GTIN	3606480776434
Returnability	Yes
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	7.28 in (18.500 cm)
Package 1 Width	10.43 in (26.500 cm)
Package 1 Length	12.99 in (33.000 cm)
Package weight(Lbs)	6.896 lb(US) (3.128 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	90
Package 2 Height	59.06 in (150.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	676.820 lb(US) (307.000 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	24
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Average percentage of recycled plastic content	37 %
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	2afadc3c-d04d-4184-9d1f-3abc2fc1a548
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions




Image of product / Alternate images

Alternative



Image of product in real life situation



Offer Marketing Illustration

Packaging

