

Product data sheet

Specifications



Reverser block, TeSys Ultra, 38A,
690VAC, 110 to 240VAC/DC coil,
for side mounting

LU6MB0FU

Main

Range	TeSys
Device short name	LU6MB
Product or component type	Reverser block
Device mounting	Separate mounting
Device application	Motor control
[Ie] rated operational current	38 A
[Uc] control circuit voltage	110...240 V AC 50/60 Hz 110...220 V DC
Current consumption	1000 mA at 110...220 V DC I maximum while closing 1000 mA at 110...240 V AC I maximum while closing

Complementary

[Ue] rated operational voltage	690 V AC power circuit
Network frequency	40...60 Hz
Inrush restraint duration	25 ms AC 15 ms DC
Operating time	150 ms with change of direction 75 ms without change of direction
Standards	EN 60947-6-2 IEC 60947-6-2 UL 60947-4-1, with phase barrier CSA C22.2 No 60947-4-1, with phase barrier
Product certifications	CE UL CSA CCC EAC ASEFA ATEX Marine
[Ui] rated insulation voltage	690 V conforming to IEC 60947-6-2 600 V conforming to UL 60947-4-1 600 V conforming to CSA C22.2 No 60947-4-1
[Uiimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-6-2
Fixing mode	Clipped (DIN rail) Screw-fixed (plate)

Connections - terminals	Control circuit: screw clamp terminals 1 cable(s) 0.34...1.5 mm ² (external diameter: 3 mm) flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 0.75...1.5 mm ² (external diameter: 3 mm) flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 0.75...1.5 mm ² (external diameter: 3 mm) rigid Control circuit: screw clamp terminals 2 cable(s) 0.34...1.5 mm ² (external diameter: 3 mm) flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 0.75...1.5 mm ² (external diameter: 3 mm) flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 0.75...1.5 mm ² (external diameter: 3 mm) rigid Power circuit: screw clamp terminals 1 cable(s) 1...10 mm ² (external diameter: 4 mm) rigid Power circuit: screw clamp terminals 1 cable(s) 1...6 mm ² (external diameter: 4 mm) flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 2.5...10 mm ² (external diameter: 4 mm) flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 1...6 mm ² (external diameter: 4 mm) flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1...6 mm ² (external diameter: 4 mm) rigid Power circuit: screw clamp terminals 2 cable(s) 1.5...6 mm ² (external diameter: 4 mm) flexible without cable end
Tightening torque	Control circuit: 0.8...1.2 N.m flat screwdriver 5 mm Control circuit: 0.8...1.2 N.m Philips No 2 screwdriver 5 mm Power circuit: 1.9...2.5 N.m flat screwdriver 6 mm Power circuit: 1.9...2.5 N.m Philips No 2 screwdriver 6 mm Power circuit: 1.9...2.5 N.m pozidriv No 2 screwdriver 6 mm
Width	45 mm
Height	115 mm
Depth	113 mm
Product weight	0.425 kg
Compatibility code	LU6MB

Environment

IP degree of protection	IP20 conforming to IEC 60947-1 (front panel and wired terminals) IP20 conforming to IEC 60947-1 (other faces) IP40 conforming to IEC 60947-1 (front panel outside connection zone)
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-25...60 °C with LUCM -25...70 °C with LUCA, LUCB, LUCC, LUCD
Ambient air temperature for storage	-40...85 °C
Fire resistance	960 °C parts supporting live components conforming to IEC 60695-2-12 650 °C conforming to IEC 60695-2-12
Operating altitude	2000 m
Shock resistance	10 gn power poles open conforming to IEC 60068-2-27 15 gn power poles closed conforming to IEC 60068-2-27
Vibration resistance	2 gn (f= 5...300 Hz) power poles open conforming to IEC 60068-2-27 4 gn (f= 5...300 Hz) power poles closed conforming to IEC 60068-2-27
Resistance to electrostatic discharge	8 kV level 3, in open air conforming to IEC 61000-4-2 8 kV level 4, on contact conforming to IEC 61000-4-2
Resistance to radiated fields	10 V/m level 3 conforming to IEC 61000-4-3
Resistance to fast transients	2 kV class 3 serial link conforming to IEC 61000-4-4 4 kV class 4 all circuits except for serial link conforming to IEC 61000-4-4
Non-dissipating shock wave	1 kV serial mode conforming to IEC 60947-6-2 2 kV common mode conforming to IEC 60947-6-2
Immunity to radioelectric fields	10 V conforming to IEC 61000-4-6

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.500 cm
Package 1 Width	5.700 cm
Package 1 Length	13.000 cm
Package 1 Weight	444.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.722 kg

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint

4

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Compliant with Exemptions

SCIP Number

Ea04e023-7196-4d5e-a41f-a711a93b86d7

REACH Regulation

[REACH Declaration](#)

California proposition 65

WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](#)

Use Again

Repack and remanufacture

End of life manual availability

[End of Life Information](#)

Take-back

No

WEEE Label

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins