

Product data sheet

Specifications



Advanced control unit, TeSys Ultra, 1.25A to 5A, 3P motors, protection & diagnostic, class 10, coil 24VAC

LUCB05B

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	TeSys
Range of Product	TeSys Ultra
Product name	TeSys Ultra
Device short name	LUCB
Product or Component Type	Advanced control unit
Device Application	Motor control Motor protection
Product Specific Application	Basic protection and advanced functions, communication
main function available	Earth fault protection Protection against phase failure and phase imbalance Manual reset Protection against overload and short-circuit
Product compatibility	Power base LUB12 Power base LUB32 Power base LUB38 Power base LUB120 Power base LUB320 Power base LUB380 Reversing contactor breaker LU2B12B Reversing contactor breaker LU2B32B
[Ue] rated operational voltage	690 V AC
Network frequency	40...60 Hz
Load type	3-phase motor self-cooled
Utilisation category	AC-43 AC-44 AC-41
Motor power kW	1.5 kW 400...440 V AC 50/60 Hz 2.2 kW 500 V AC 50/60 Hz 3 kW 690 V AC 50/60 Hz
rated motor current adjustment range	1.25...5 A
Thermal overload class	Class 10 40...60 Hz -13...158 °F (-25...70 °C) IEC 60947-6-2 Class 10 40...60 Hz -13...158 °F (-25...70 °C) UL 508
Tripping threshold	14.2 x Ir +/- 20 %
Phase failure sensitivity	Yes
[Uc] control circuit voltage	24 V AC

Complementary

Control circuit voltage limits	20...26.5 V AC 24 V in operation 14.5 V AC 24 V drop-out
--------------------------------	---

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Typical current consumption	140 mA 24 V AC I maximum while closing with LUB12 220 mA 24 V AC I maximum while closing with LUB32 220 mA 24 V AC I maximum while closing with LUB38 70 mA 24 V AC I rms sealed with LUB12 90 mA 24 V AC I rms sealed with LUB32 90 mA 24 V AC I rms sealed with LUB38
Heat dissipation	2 W control circuit with LUB12 3 W control circuit with LUB32 3 W control circuit with LUB38
Operating time	35 ms opening with LUB12 control circuit 35 ms opening with LUB32 control circuit 35 ms opening with LUB38 control circuit 70 ms closing with LUB12 control circuit 70 ms closing with LUB32 control circuit 70 ms closing with LUB38 control circuit
Reset	Manual reset
Standards	EN 60947-6-2 IEC 60947-6-2 UL 60947-4-1, with phase barrier CSA C22.2 No 60947-4-1, with phase barrier
Product Certifications	CE UL CSA CCC EAC ASEFA ATEX Marine
[Ui] rated insulation voltage	690 V IEC 60947-6-2 600 V UL 60947-4-1 600 V CSA C22.2 No 60947-4-1
[Uimp] rated impulse withstand voltage	6 kV IEC 60947-6-2
Safe separation of circuit	400 V SELV between the control and auxiliary circuits IEC 60947-1 400 V SELV between the control or auxiliary circuit and the main circuit IEC 60947-1
Fixing mode	Plug-in (front face)
Width	1.8 in (45 mm)
Height	2.6 in (66 mm)
Depth	2.4 in (60 mm)
Compatibility code	LUCB

Environment

IP degree of protection	IP20 front panel and wired terminals IEC 60947-1 IP20 other faces IEC 60947-1 IP40 front panel outside connection zone IEC 60947-1
Protective treatment	TH IEC 60068
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Operating altitude	6561.68 ft (2000 m)
Fire resistance	1760 °F (960 °C) parts supporting live components IEC 60695-2-12 1202 °F (650 °C) IEC 60695-2-12
Shock resistance	10 gn power poles open IEC 60068-2-27 15 gn power poles closed IEC 60068-2-27
Vibration resistance	2 gn 5...300 Hz power poles open IEC 60068-2-6 4 gn 5...300 Hz power poles closed IEC 60068-2-6
Resistance to electrostatic discharge	8 kV 3 in open air IEC 61000-4-2 8 kV 4 on contact IEC 61000-4-2

Non-dissipating shock wave	1 kV serial mode IEC 60947-6-2 2 kV common mode IEC 60947-6-2
Resistance to radiated fields	9.1 V/m (10 V/m) 3 IEC 61000-4-3
Resistance to fast transients	2 kV 3 serial link IEC 61000-4-4 4 kV 4 all circuits except for serial link IEC 61000-4-4
Immunity to radioelectric fields	10 V IEC 61000-4-6
Immunity to microbreaks	3 ms
Immunity to voltage dips	70 % / 500 ms IEC 61000-4-11

Ordering and shipping details

Category	US10I1122397
Discount Schedule	0I11
GTIN	3389110364149
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	3.23 in (8.200 cm)
Package 1 Length	3.39 in (8.600 cm)
Package weight(Lbs)	3.986 oz (113.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	23
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	6.393 lb(US) (2.900 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) **19**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Compliant with Exemptions

SCIP Number 0f22867c-27de-46b9-965c-a40bbb8a3f0a

REACH Regulation [REACH Declaration](#)

Halogen content performance Halogen free plastic parts product

PVC free Yes

Use Again

Repack and remanufacture

Circularity Profile [End of Life Information](#)

Take-back No

WEEE Label  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.