

Product data sheet

Specifications



pre assembled relay, Harmony Solid State Relays, 2A, zero voltage switching, screw sockets, input 4 to 12V DC, output 24 to 250V AC

SSL1A12JDPV

Main

Range of product	Harmony Solid State Relays
Device short name	SSL
Network number of phases	1 phase
[Uc] control circuit voltage	4...12 V
Connections - terminals	Screw connectors
Output switching mode	Zero voltage switching

Complementary

Mounting support	Screw socket
[In] rated current	2 A
Output voltage	24...250 V AC
[Uc] control circuit voltage	4...12 V DC
CLAMPING FORCE	< 0.5 N.m 4.4 lb-in
Connections - terminals	Flexible cable with cable end, clamping capacity: 0.2...2.5 mm ² (AWG 24...AWG 14) Solid cable with cable end, clamping capacity: 0.2...2.5 mm ² (AWG 24...AWG 14)
Capacitance unbalance	1.5 pF input/output
Minimum switching voltage	4 V DC turn-on
Maximum switching voltage	1 V DC turn-off
Input impedance	333 kOhm
Solid state output type	Zero voltage switching SCR output
Load current	0.07...2 A
Transient Overvoltage	600 V AC
Surge current	120 A for 16.6 ms 115 A for 20 ms
Maximum voltage drop	<1.1 V on-state
Maximum I ² t for fusing	285 A ² .s for 10 ms at 50 Hz 260 A ² .s for 8.3 ms at 60 Hz
Maximum leakage current	4 mA off-state
DV/dt	500 V/μs off-state at maximum voltage
Response time	0.5 cycle (turn-on) 0.5 cycle (turn-off)
Overvoltage category	III

Width	6.2 mm
Height	96.5 mm
Depth	79.5 mm
Product weight	0.0285 kg
Device presentation	Complete product

Environment

Flame retardance	V0 conforming to UL 94
Dielectric strength	2500 V for input/output
Pollution degree	2
Standards	IEC 60950-1 IEC 61000 IEC 62314 IEC 61984 EN 61984
Product certifications	UL CSA CE UL 508 CSA22.2 No. 14-10 GOST
Marking	CURus CSA CE EAC
IP degree of protection	IP20
Ambient air temperature for operation	-20...70 °C
Ambient air temperature for storage	-20...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.600 cm
Package 1 Width	8.000 cm
Package 1 Length	9.700 cm
Package 1 Weight	27.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	30
Package 2 Height	9.000 cm
Package 2 Width	10.000 cm
Package 2 Length	20.000 cm
Package 2 Weight	902.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	60
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm

Package 3 Weight 2.603 kg

Contractual warranty

Warranty 18 Months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint

10

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

Use Again


Repack and remanufacture

Take-back


No

Dimensions Drawings

Dimensions



Performance Curves

Derating Curves

X : Ambient Temperature (°C)

Y : Load Current (Amperes)

1 : Installed single unit, distance to adjacent components more than 6.2 mm

2 : Multiple units, no minimum spacing between components

Technical Illustration

Dimensions





Image of product / Alternate images

Alternative








Image of product in real life situation

