

# Product data sheet

Specifications



IEC contactor,Easy TeSys  
DPE,nonreversing,32A,3P,15HP at  
480V AC,24V 50/60Hz coil

DPE32B7

Product availability: Stock - Normally stocked in distribution facility

## Main

Range	Easy TeSys
Product name	Easy TeSys DPE
Product or Component Type	Contactor
Device short name	DPE
Contactor application	Resistive load Motor control
Utilisation category	AC-4 AC-1 AC-3
Poles description	3P
Pole contact composition	3 NO
Auxiliary contact composition	1 NO
[Ie] rated operational current	32 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 40 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
[Uc] control circuit voltage	24 V AC 50/60 Hz
Motor power kW	7.5 kW 220...230 V AC 50/60 Hz 15 kW 380...400 V AC 50/60 Hz 15 kW 415 V AC 50/60 Hz 15 kW 440 V AC 50/60 Hz 18.5 kW 500 V AC 50/60 Hz 18.5 kW 660...690 V AC 50/60 Hz
Maximum Horse Power Rating	2 hp at 115 V AC 50/60 Hz for 1 phase motors 3 hp at 230/240 V AC 50/60 Hz for 1 phase motors 7.5 hp at 200/208 V AC 50/60 Hz for 3 phase motors 7.5 hp at 230/240 V AC 50/60 Hz for 3 phase motors 15 hp at 460/480 V AC 50/60 Hz for 3 phase motors 20 hp at 575/600 V AC 50/60 Hz for 3 phase motors

## Complementary

Maximum Operational Voltage	Power circuit <= 690 V AC 25...400 Hz Power circuit <= 300 V DC
[Ith] conventional free air thermal current	10 A (at 140 °F (60 °C)) for signalling circuit 40 A (at 140 °F (60 °C)) for power circuit
Irms rated making capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 450 A at 440 V for power circuit conforming to IEC 60947
Rated breaking capacity	450 A at 440 V for power circuit conforming to IEC 60947
Associated fuse rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 40 A gG at <= 690 V coordination type 2 for power circuit
Average impedance	2 mOhm - Ith 40 A 50 Hz for power circuit

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Power dissipation per pole</b>	3.2 W AC-1 1.25 W AC-3
<b>Electrical durability</b>	1 Mcycles 32 A AC-3 <= 440 V 0.6 Mcycles 40 A AC-1 <= 440 V
<b>Safety reliability level</b>	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
<b>Control circuit type</b>	AC 50/60 Hz
<b>Coil technology</b>	Without built-in suppressor module
<b>Control circuit voltage limits</b>	Drop-out: 0.3...0.6 Uc at 50/60 Hz (at <158 °F (70 °C)) Operational: 0.8...1.1 Uc at 50 Hz (at <140 °F (60 °C)) Operational: 0.85...1.1 Uc at 60 Hz (at <140 °F (60 °C)) Operational: 1...1.1 Uc at 50/60 Hz (at <158 °F (70 °C))
<b>Inrush power in VA</b>	70 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 70 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
<b>Hold-in power consumption in VA</b>	7.5 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 7 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
<b>Heat dissipation</b>	2...3 W 50/60 Hz
<b>Operating time</b>	12...22 ms closing 4...19 ms opening
<b>Mechanical durability</b>	10 Mcycles
<b>Maximum operating rate</b>	3600 cyc/h 140 °F (60 °C)
<b>Auxiliary contacts type</b>	Mechanically linked 1 NO IEC 60947-5-1
<b>Minimum switching current</b>	5 mA for signalling circuit
<b>Minimum switching voltage</b>	17 V for signalling circuit
<b>Insulation resistance</b>	> 10 MΩ for signalling circuit
<b>Non-overlap time</b>	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
<b>Signalling circuit frequency</b>	25...400 Hz
<b>Connections - terminals</b>	Control circuit: screw clamp terminals 1 0.002...0.006 in <sup>2</sup> (1...4 mm <sup>2</sup> ) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.002...0.006 in <sup>2</sup> (1...4 mm <sup>2</sup> ) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 0.002...0.006 in <sup>2</sup> (1...4 mm <sup>2</sup> ) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 0.002...0.004 in <sup>2</sup> (1...2.5 mm <sup>2</sup> ) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.002...0.006 in <sup>2</sup> (1...4 mm <sup>2</sup> ) - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 0.002...0.006 in <sup>2</sup> (1...4 mm <sup>2</sup> ) - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 0.004...0.02 in <sup>2</sup> (2.5...10 mm <sup>2</sup> ) - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 2 0.004...0.02 in <sup>2</sup> (2.5...10 mm <sup>2</sup> ) - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 0.002...0.02 in <sup>2</sup> (1...10 mm <sup>2</sup> ) - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 0.002...0.009 in <sup>2</sup> (1.5...6 mm <sup>2</sup> ) - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 0.002...0.02 in <sup>2</sup> (1.5...10 mm <sup>2</sup> ) - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 0.004...0.02 in <sup>2</sup> (2.5...10 mm <sup>2</sup> ) - cable stiffness: solid without cable end
<b>Tightening torque</b>	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2 Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2
<b>Mounting Support</b>	Rail Plate
<b>Height</b>	3.3 in (85 mm)

Width	1.8 in (45 mm)
Depth	3.6 in (92 mm)
Net Weight	0.82 lb(US) (0.37 kg)

## Environment

[Ui] rated insulation voltage	Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL
Overvoltage category	III
Pollution degree	3
[Ui <sub>imp</sub> ] rated impulse withstand voltage	6 kV IEC 60947
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 60947-4-1
Product Certifications	UL CSA
IP degree of protection	IP20 front face IEC 60529
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Ambient air temperature for operation	-40...140 °F (-40...60 °C)
Operating altitude	0...6561.68 ft (0...2000 m)
Fire resistance	1562 °F (850 °C) IEC 60695-2-1
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz) Vibrations contactor closed 4 Gn, 5...300 Hz) Shocks contactor open 10 Gn for 11 ms) Shocks contactor closed 15 Gn for 11 ms)

## Ordering and shipping details

Category	US10I1322362
Discount Schedule	0I13
GTIN	3606485332680
Returnability	Yes
Country of origin	ID

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.20 in (5.590 cm)
Package 1 Width	3.80 in (9.650 cm)
Package 1 Length	4.70 in (11.940 cm)
Package weight(Lbs)	14.815 oz (420.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	16

<b>Package 2 Height</b>	5.91 in (15.000 cm)
<b>Package 2 Width</b>	11.81 in (30.000 cm)
<b>Package 2 Length</b>	15.75 in (40.000 cm)
<b>Package 2 Weight</b>	15.225 lb(US) (6.906 kg)
<b>Unit Type of Package 3</b>	P06
<b>Number of Units in Package 3</b>	256
<b>Package 3 Height</b>	29.53 in (75.000 cm)
<b>Package 3 Width</b>	23.62 in (60.000 cm)
<b>Package 3 Length</b>	31.50 in (80.000 cm)
<b>Package 3 Weight</b>	261.239 lb(US) (118.496 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) **26**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Compliant**

REACH Regulation [REACH Declaration](#)

California proposition 65 **WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](#)**

PVC free **Yes**

## Use Again

### Repack and remanufacture

Circularity Profile [End of Life Information](#)

Take-back **No**

WEEE Label  **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.**

Image of product / Alternate images

Alternative

---



