

Product data sheet

Specifications

SQUARE D



Plug in relay, Type KP, tubular, 1 HP at 277 VAC, 10A resistive at 120 VAC, 11 pin, 3PDT, 3 NO, 3 NC, 120 VAC coil

8501KPR13V20

Product availability: Stock - Normally stocked in distribution facility

Main

| | |
|------------------------------|---------------------|
| product range | 8501K |
| product type | Relay |
| Relay Type | General purpose |
| mounting type | Socket |
| contact composition | 3PDT |
| [Uc] control circuit voltage | 120 V AC |
| pilot light | No indicator |
| manual operator | Without test button |

Complementary

| | |
|---------------------------|---|
| horsepower rating | 1 hp 277 V AC 0.33 hp 120 V AC |
| breaking capacity | 3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 10 A 277 V AC resistive control circuit UL 508 10 A 30 V DC resistive control circuit UL 508 |
| maximum switching voltage | 300 V AC 30 V DC |
| contact material | Silver alloy (AgNi) |
| operating time | 20 ms - pick-up 20 ms - drop-out |
| shape of pins | Tubular |
| for use with | 8501NR62 8501NR61 |

Environment

| | |
|---|---|
| ambient temperature range - operational | -40...55 °C (-40...131 °F) |
| product certifications | UL Listed UL Recognized CSA CE |
| Height | 2.66 in (67.56 mm) |
| Width | 1.4 in (35.6 mm) |
| Depth | 1.4 in (35.6 mm) |

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------|--------------|
| Category | US10CP221141 |
| Discount Schedule | OCP2 |
| GTIN | 785901219743 |
| Returnability | Yes |
| Country of origin | CN |

Packing Units

| | |
|------------------------|---------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 1.70 in (4.318 cm) |
| Package 1 Width | 1.70 in (4.318 cm) |
| Package 1 Length | 3.00 in (7.62 cm) |
| Package weight(Lbs) | 3.360 oz (95.254 g) |



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

| | |
|--|----|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 25 |
|--|----|

Use Better

Materials and Substances

| | |
|--|----|
| Packaging made with recycled cardboard | No |
|--|----|

| | |
|--------------------------------------|----|
| Packaging without single use plastic | No |
|--------------------------------------|----|

| | |
|-----------------------------------|--|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
|-----------------------------------|--|

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

Repack and remanufacture

| | |
|---------------------|--|
| Circularity Profile | No need of specific recycling operations |
|---------------------|--|

| | |
|-----------|----|
| Take-back | No |
|-----------|----|

Dimensions Drawings

Approximate Dimensions

Connections and Schema

Connections and Wiring Diagrams

8501KP13***




Image of product / Alternate images

Alternative



