

Product data sheet

Specifications



Pilot light, Harmony 9001K, metal, polycarbonate, domed, red, 30mm, 24-28V

9001KP35R9

Main

Range of product Harmony 9001K

Product or component type Pilot light

Device short name 9001K

Complementary

Bezel material Metal

Mounting diameter 30 mm

Shape of signaling unit head Round

Lens type Domed plastic

Cap/operator or lens colour Red

Light source incandescent

Bulb base BA 9s

Light block supply Direct 24...28 V AC/DC

Connections - terminals Screw clamp terminals, 1 x 0.22...2 x 1.5 mm² conforming to IEC 60947-1

Tightening torque 0.8 N.m conforming to IEC 60947-1

Shape of screw head Cross slotted

Shape of screw head Cross slotted

Operating position Any position

[Ui] rated insulation voltage 250 V (pollution degree 2) conforming to IEC 60947-1

[Uiimp] rated impulse withstand voltage 2.5 kV conforming to IEC 60947-1

Short-circuit protection 10 A cartridge fuse conforming to IEC 60947-5-1

Light source Incandescent bulb

[Ith] conventional free air thermal current 10 A

CAD overall width 54 mm

CAD overall height 70 mm

CAD overall depth 42 mm

[Us] rated supply voltage 24...28 V AC/DC

Product weight 0.134 kg

Device presentation Complete product

Lens type Domed

[Us] rated supply voltage 24...28 V

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Light block supply	Full voltage
Lens material	Polycarbonate
Size	30 mm

Environment

Standards	JIS C8201-5-1 CSA C22.2 No 14 JIS C 852 EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 UL 508 JIS C8201-1
Product certifications	UL 508 NEMA
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Vibration resistance	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 6

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.499 cm
Package 1 Width	9.299 cm
Package 1 Length	5.7 cm
Package 1 Weight	145.15 g
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	3.633 kg

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Dimensions



e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.