

Product data sheet

Specifications



EMC radio interference input filter - for variable speed drive

VW3A4416

Main

Range of product	Altivar
Product or component type	EMC input filter
Range compatibility	Altivar 12
Product compatibility	ATV12H018F1 ATV12H018M2 ATV12H037F1 ATV12H037M2 ATV12H055M2 ATV12H075M2 ATV12P037F1 ATV12P037M2 ATV12P055M2 ATV12P075M2
Product specific application	Radio interference input filter

Complementary

Product weight	1.12 kg
----------------	---------

Environment

Standards	Environment 1 category C2 IEC 61800-3 Environment 1 category C3 IEC 61800-3 Environment 2 category C3 IEC 61800-3
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	19.000 cm
Package 1 Length	38.500 cm
Package 1 Weight	1.108 kg
Unit Type of Package 2	P06
Number of Units in Package 2	24
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	32.500 kg

Contractual warranty

Warranty

18 months



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

Repack and remanufacture

Take-back	No
-----------	----

Dimensions Drawings

Dimensions



Dimensions in mm

a	b	c	G	H
75	194	30	61	180

Dimensions in in.

a	b	c	G	H
2.95	7.64	1.18	2.40	7.09