

Product data sheet

Specifications



Additional pole, TeSys Control, 20A, for V01

VZ01

Main

Range	TeSys
Device short name	VZ
Product or component type	Additional pole
Performance level	High performance
Poles description	1P
Contacts type and composition	1 NO
Product compatibility	V01
Range compatibility	TeSys TeSys VARIO switch disconnecter
Network type	DC AC
Network frequency	50/60 Hz
Suitability for isolation	Yes

Complementary

Mounting location	Left Right
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	20 A
[Ithe] conventional enclosed thermal current	16 A
Mechanical durability	100000 cycles
Electrical durability	100000 cycles AC-21 30000 cycles DC-1...5
Connections - terminals	Power circuit: screw clamp terminals6 mm² - flexible - with cable end Power circuit: screw clamp terminals10 mm² - solid
Tightening torque	Power circuit: 2.1 N.m - on screw clamp terminals
Height	74 mm
Width	16 mm
Depth	35 mm
Product weight	0.05 kg

Environment

Standards	IEC 60947-3
-----------	-------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product certifications	GL CSA UL UKCA
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C
Fire resistance	960 °C conforming to IEC 60695-2-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	9.0 cm
Package 1 Length	5.5 cm
Package 1 Weight	46.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	69
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.576 kg

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	65661eb0-9ea7-4d52-b0a4-16b981f28f63
REACH Regulation	REACH Declaration
Halogen-free status	Halogen free product
PVC free	Yes

Use Again

Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Assembly's dimensions

