

# Product data sheet

Specifications



Auxiliary contact block, TeSys Deca,  
2NO, front mounting, screw clamp  
terminals

LADN20

## Main

Range	TeSys TeSys Deca
Product name	TeSys Deca
Product or component type	Auxiliary contact block
Device short name	LADN
Range compatibility	TeSys D CAD TeSys D LC1D TeSys F LC1F TeSys F CR1F TeSys Deca CAD TeSys Deca LC1D
Mounting location	Front
Pole contact composition	2 NO
Contacts operation	Instantaneous
[Ue] rated operational voltage	690 V AC 25...400 Hz
[Ie] rated operational current	6 A at 120 V AC-15 1.04 A at 690 V AC-15 0.55 A at 125 V DC-13 0.1 A at 600 V DC-13
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1 600 V conforming to UL 600 V conforming to CSA
[ith] conventional free air thermal current	10 A (at 60 °C)
Standards	EN/IEC 60947-5-1 GB/T 14048.5 EN 50012 UL 60947-5-1 CSA C22.2 No 60947-5-1 IEC 60335-1:Clause 30.2 IEC 60335-2-40:Annex JJ UL 60335-2-40:Annex JJ
Product certifications	CB Scheme UL CSA CCC EAC UKCA

## Complementary

Irms rated making capacity	140 A AC conforming to IEC 60947-5-1 250 A DC conforming to IEC 60947-5-1
Permissible short-time rating	100 A 60 °C 1 s 120 A 60 °C 500 ms 140 A 60 °C 100 ms

<b>Protection type</b>	GG fuse 10 A
<b>Mechanical durability</b>	30 Mcycles
<b>Minimum switching current</b>	5 mA
<b>Minimum switching voltage</b>	17 V
<b>Non-overlap time</b>	1.5 ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact
<b>Insulation resistance</b>	> 10 MΩ
<b>Connections - terminals</b>	Screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> flexible with cable end Screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> flexible without cable end Screw clamp terminals 2 cable(s) 1...2.5 mm <sup>2</sup> flexible with cable end Screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> flexible without cable end Screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> rigid without cable end Screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> rigid without cable end
<b>Tightening torque</b>	1.7 N.m - with screwdriver flat Ø 6 mm 1.7 N.m - with screwdriver Philips No 2 1.7 N.m - with screwdriver pozidriv No 2
<b>Height</b>	48 mm
<b>Width</b>	26 mm
<b>Depth</b>	42 mm
<b>Colour</b>	Dark grey

## Environment

<b>Environmental characteristic</b>	Normal environment
<b>IP degree of protection</b>	IP20 conforming to IEC 60529
<b>Protective treatment</b>	TH conforming to IEC 60068
<b>Ambient air temperature for storage</b>	-60...80 °C
<b>Ambient air temperature for operation</b>	-5...60 °C
<b>Operating altitude</b>	3000 m

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	5.000 cm
<b>Package 1 Width</b>	2.800 cm
<b>Package 1 Length</b>	4.300 cm
<b>Package 1 Weight</b>	34.000 g
<b>Unit Type of Package 2</b>	S03
<b>Number of Units in Package 2</b>	320
<b>Package 2 Height</b>	30.000 cm
<b>Package 2 Width</b>	30.000 cm
<b>Package 2 Length</b>	40.000 cm
<b>Package 2 Weight</b>	11.413 kg
<b>Unit Type of Package 3</b>	P06
<b>Number of Units in Package 3</b>	2560
<b>Package 3 Height</b>	75.000 cm

Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	98.500 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint 4

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Compliant

REACH Regulation [REACH Declaration](#)

## Use Again

### Repack and remanufacture

End of life manual availability No need of specific recycling operations

Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins