

# Product data sheet

Specifications



## Climasys Ultra thin resistance heater low starting current 20W 240V 130x250mm

NSYCRS25W240V

### Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Ultra thin resistance heater
Power range	25 W
Input voltage	240 V AC 50/60 Hz
Electrical connection	Cable length: 2 m

### Complementary

Operating position	Vertical Horizontal
Ambient air temperature for operation	-60...70 °C
Temperature setting range	-40...70 °C
Material	Silicone rubber
Height	External: 110 mm
Width	External: 230 mm
Depth	External : 1.6 mm
Device composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts fixing accessories
Condition of use	Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed
fixing mode	By 4 screws
Mounting support	Standard mounting plate DIN rail Adhesive Velcro Telequick mounting plate

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	25.500 cm
Package 1 Length	28.000 cm

Package 1 Weight	302.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Height	32.000 cm
Package 2 Width	51.000 cm
Package 2 Length	65.000 cm
Package 2 Weight	7.550 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	325
Package 3 Height	171.000 cm
Package 3 Width	100.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	115.000 kg

## Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **No**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant with Exemptions**

SCIP Number **60bb7229-9ac3-41cb-896e-a93aa448ebf8**

REACH Regulation [REACH Declaration](#)

## Use Again

### Repack and remanufacture

End of life manual availability **No need of specific recycling operations**

Take-back **No**

WEEE Label **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**