

# Product data sheet

Specifications



Push-to-test pilot light, Harmony 9001SK, plastic, polycarbonate, domed, amber, 30mm, LED yellow, 120V

9001SKT38LYA9

## Main

Range of product	Harmony 9001SK
Product or component type	Push-to-test pilot light
Device short name	9001SK
Lens type	Domed plastic
Light block supply	Direct 120 V AC/DC

## Complementary

Bezel material	Plastic
Mounting diameter	30 mm
Shape of signaling unit head	Round
Cap/operator or lens colour	Amber
Light source	Yellow LED
Bulb base	BA 9s
[Us] rated supply voltage	120 V AC/DC
Tightening torque	0.8 N.m conforming to IEC 60947-1
Shape of screw head	Cross slotted
Connections - terminals	Screw clamp terminals, 1 x 0.22...2 x 1.5 mm <sup>2</sup> conforming to IEC 60947-1
[Ith] conventional free air thermal current	10 A
Short-circuit protection	10 A cartridge fuse conforming to IEC 60947-5-1
[Ui] rated insulation voltage	250 V (pollution degree 2) conforming to IEC 60947-1
[Uiimp] rated impulse withstand voltage	2.5 kV conforming to IEC 60947-1
Operating position	Any position
Operating mode	Push-to-test
CAD overall width	54 mm
CAD overall height	70 mm
CAD overall depth	42 mm
Net weight	0.181 kg
Lens type	Domed
[Us] rated supply voltage	120 V
Light source colour	Yellow
Contacts type and composition	1 C/O

<b>Lens material</b>	Polycarbonate
<b>Size</b>	30 mm
<b>Light source</b>	LED

## Environment

<b>Electrical shock protection class</b>	Class II conforming to IEC 61140
<b>Protective treatment</b>	TC
<b>IP degree of protection</b>	IP66 conforming to IEC 60529
<b>NEMA degree of protection</b>	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
<b>Vibration resistance</b>	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
<b>Shock resistance</b>	50 gn conforming to IEC 60068-2-27
<b>Ambient air temperature for operation</b>	-25...70 °C
<b>Ambient air temperature for storage</b>	-40...70 °C
<b>Standards</b>	IEC 60947-5-1 UL 508 IEC 60947-5-4 JIS C 852 JIS C8201-5-1 IEC 60947-1 CSA C22.2 No 14 JIS C8201-1
<b>Product certifications</b>	UL 508 NEMA

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	5.080 cm
<b>Package 1 Width</b>	6.096 cm
<b>Package 1 Length</b>	11.430 cm
<b>Package 1 Weight</b>	122.470 g



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	<b>WARNING:</b> This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>

## Use Again

### Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins