

Product data sheet

Characteristics

AP8714SX592

Power Cord Kit (6 ea), Locking, C19 to C20,
1.2m, Blue



Overview

Lead time Usually in Stock



Main

Input Connection Type	IEC 60320 C20
Cable length	4 ft (1.22 m)
Number of cables	6

Physical

Color	Blue
Height	11.81 in (30 cm)
Width	2.76 in (7 cm)
Depth	2.76 in (7 cm)
Net Weight	3.62 lb(US) (1.64 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Max line current	16 A
Input current limits	16 A

Output

Maximum Total Current Draw per Phase	16 A
Number of power socket outlets	1 IEC 60320 C19
Cord Length	4 ft (1.22 m)

Conformance

Product Certifications	CCC CSA PSE UL Listed VDE
------------------------	---------------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental

Ambient Air Temperature for Operation	32...167 °F (0...75 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...167 °F (-25...75 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304285007
Package weight(Lbs)	3.62 lb(US) (1.64 kg)

Packing Units

Package 1 Height	11.81 in (30 cm)
Package 1 width	2.76 in (7 cm)
Package 1 Length	2.76 in (7 cm)
SCC14	10731304285004
Number of Units in Package 3	270

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------