

Product data sheet

Characteristics

GUPXCK100F

NEMA 12 (IP54) Filters Kit for GUTOR PXC UL 75/100 kVA UPS



Overview

Presentation	Dust filter kits to achieve NEMA type 12 (IP54) protection rating for 75-100kVA UPS solutions
Lead time	Usually in Stock

Physical

Height	8.50 in (21.6 cm)
Width	8.50 in (21.6 cm)
Depth	0.39 in (1 cm)
Net Weight	0.99 lb(US) (0.45 kg)
Mounting Mode	Not rack-mountable

Conformance

Standards	FCC Part 15 class A UL 1778
-----------	--------------------------------

Environmental

Ambient Air Temperature for Operation	14...104 °F (-10...40 °C)
Operating altitude	0...9842 ft
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage altitude	0...16404 ft (0.00...4999.94 m)
Storage Relative Humidity	0...95 % Non-condensing

Ordering and shipping details

Nbr. of units in pkg.	1
Package weight(Lbs)	2.00 lb(US) (0.908 kg)

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.00 in (25.4 cm)
Package 1 width	10.00 in (25.4 cm)
Package 1 Length	7.99 in (20.3 cm)

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------