

Product data sheet

Characteristics

TCSECN300R2

ConneXium Ethernet copper cable for Ethernet network - 300 m



Main

Range of Product	ConneXium
Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Product or Component Type	Ethernet copper cable
Accessory / separate part destination	Ethernet network
Cable length	984.25 ft (300 m)
Cable packaging	Roll

Complementary

Transmission rate	100 Mbit/s 262.47 ft (80 m)
Transmission support medium	Double shielded twisted pair
AWG Gauge	AWG 24
Marking	CE
Conductor material	Copper

Environment

Standards	EN 50173 class D UL 508-CM EIA/TIA-568 category CAT 5E
-----------	--

Ordering and shipping details

Category	18225-PLC NTWRK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	3595863925470
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.84 in (25.0 cm)
Package 1 Width	14.57 in (37.0 cm)
Package 1 Length	14.57 in (37.0 cm)
Package 1 Weight	29.37 lb(US) (13.32 kg)
Unit Type of Package 2	P12
Number of Units in Package 2	10
Package 2 Height	25.59 in (65.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	293.66 lb(US) (133.2 kg)

Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  [EU RoHS Declaration](#)

Toxic heavy metal free

Yes

Mercury free

Yes

China RoHS Regulation

 [China RoHS Declaration](#)

RoHS exemption information

 Yes

Environmental Disclosure

 [Product Environmental Profile](#)

Contractual warranty

Warranty

18 months