

Product data sheet

Characteristics

8910DPA92V09

Contactor, Definite Purpose, 90A, 2 pole, 20 HP at 230 VAC, 1 phase, 208/240 VAC 60 Hz 220 VAC 50 Hz coil, open



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	90 A
Number of Poles	2P
Pole contact composition	2 NO
Range of Product	DPA

Complementary

Maximum Horse Power Rating	7.5 Hp 115 V AC, 1 phase 20 hp 230 V AC, 1 phase
Locked rotor rated current	540 A 277 V AC 450 A 460 V AC 360 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	208...240 V AC 60 Hz 220 V AC 50 Hz
Phase	1 phase
Electrical Connection	Quick connect terminals Box lugs

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21349-8910 DPA 9_(90 AMP)
Discount Schedule	CP1B
GTIN	785901024552
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.10 in (15.494 cm)
Package 1 Width	6.60 in (16.764 cm)
Package 1 Length	7.10 in (18.034 cm)
Package 1 Weight	3.36 lb(US) (1.524 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------
