

Product data sheet

Characteristics

8910DPA93V06

Contactor, Definite Purpose, 90A, 3 pole, 50 HP at 575 VAC, 3 phase, 440/480 VAC 50/60 Hz coil, open



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	90 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA

Complementary

Maximum Horse Power Rating	7.5 Hp 115 V AC, 1 phase 20 Hp 230 V AC, 1 phase 30 Hp 230 V AC, 3 phase 50 Hp 460 V AC, 3 phase 50 hp 575 V AC, 3 phase
Locked rotor rated current	540 A 277 V AC 450 A 460 V AC 360 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	440 V AC 50 Hz 480 V AC 60 Hz
Phase	3 phase
Electrical Connection	Quick connect terminals Box lugs

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21349-8910 DPA 9_(90 AMP)
Discount Schedule	CP1B
GTIN	785901024576
Nbr. of units in pkg.	1
Package weight(Lbs)	3.68 lb(US) (1.669 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.80 in (14.732 cm)
Package 1 width	5.60 in (14.224 cm)
Package 1 Length	7.00 in (17.78 cm)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------