

# 9001SKT38LWW9

30mm push button, Type SK, push to test pilot light, 120VAC/VDC white LED light module, white domed lens, NEMA 4, 4X



## Main

|                           |                          |
|---------------------------|--------------------------|
| Range of Product          | Harmony 9001SK           |
| Product or Component Type | Push-to-test pilot light |
| Device short name         | 9001SK                   |
| Lens type                 | Domed plastic            |
| Light block supply        | Direct 120 V AC/DC       |

## Complementary

|                                             |                                                                          |
|---------------------------------------------|--------------------------------------------------------------------------|
| Bezel material                              | Plastic                                                                  |
| Mounting diameter                           | 1.18 in (30 mm)                                                          |
| Shape of signaling unit head                | Round                                                                    |
| Cap/operator or lens colour                 | White                                                                    |
| Light source                                | White LED                                                                |
| Bulb base                                   | BA 9s                                                                    |
| [Us] rated supply voltage                   | 120 V AC/DC                                                              |
| Tightening torque                           | 7.08 lbf.in (0.8 N.m) EN/IEC 60947-1                                     |
| Shape of screw head                         | Cross slotted                                                            |
| Connections - terminals                     | Screw clamp terminals, 1 x 0.22...2 x 1.5 mm <sup>2</sup> EN/IEC 60947-1 |
| [Ith] conventional free air thermal current | 10 A                                                                     |
| Short-circuit protection                    | 10 A cartridge fuse EN/IEC 60947-5-1                                     |
| [Ui] rated insulation voltage               | 250 V 2)EN/IEC 60947-1                                                   |
| [Uimp] rated impulse withstand voltage      | 2.5 kV EN/IEC 60947-1                                                    |
| Operating position                          | Any position                                                             |
| Operating Mode                              | Push-to-test                                                             |
| CAD overall width                           | 2.13 in (54 mm)                                                          |
| CAD overall height                          | 2.76 in (70 mm)                                                          |
| CAD overall depth                           | 1.65 in (42 mm)                                                          |
| Net Weight                                  | 0.40 lb(US) (0.181 kg)                                                   |

## Environment

|                                   |                                                                                  |
|-----------------------------------|----------------------------------------------------------------------------------|
| Electrical shock protection class | Class II IEC 61140                                                               |
| Protective treatment              | TC                                                                               |
| IP degree of protection           | IP66 IEC 60529                                                                   |
| NEMA degree of protection         | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4<br>NEMA 4X |
| Vibration resistance              | 7 gn 2...500 Hz)IEC 60068-2-6                                                    |

|                                       |                                                                                                                                  |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| Shock resistance                      | 50 gn IEC 60068-2-27                                                                                                             |
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C)                                                                                                       |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                                                                                       |
| Standards                             | EN/IEC 60947-1<br>JIS C 852<br>EN/IEC 60947-5-1<br>JIS C8201-5-1<br>CSA C22.2 No 14<br>UL 508<br>EN/IEC 60947-5-4<br>JIS C8201-1 |
| Product Certifications                | NEMA<br>UL 508                                                                                                                   |

## Ordering and shipping details

|                   |                   |
|-------------------|-------------------|
| Category          | 21429-9001 SK,SKY |
| Discount Schedule | CS1               |
| GTIN              | 785901792819      |
| Returnability     | No                |
| Country of origin | MX                |

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 5.08 in (12.903 cm)  |
| Package 1 Width              | 2.00 in (5.08 cm)    |
| Package 1 Length             | 12.90 in (32.774 cm) |
| Package 1 Weight             | 8.00 oz (226.796 g)  |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                      |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                         |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                                                                                                 |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                          |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                                                                                                                                                                                                                                                                                                |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                                                                                           |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|