


# Product data sheet

## Characteristics

# ACRC600

InRow RC, 600mm, Chilled Water, 200-240V, 50/60Hz



### Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--------------------------------------------

### Main

Main Input Voltage	3 phase 3 phase
Plug standard	NEMA L21-20P
Number of rack unit	42U
Number of cables	2
Provided Equipment	Installation guide Operations and maintenance manual

### General

Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Air flow	6000 ft³/min (2831.68 l/s)
Minimum Water Inlet Temperature	45 °F (7 °C)
Condensate Pump Capacity	8.45 Gal/hr(US) (0.03 m3/h)

### Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	23.62 in (60 cm)
Depth	42.13 in (107 cm)
Net Weight	761.59 lb(US) (345.45 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Input

Input Frequency	50/60 Hz
-----------------	----------

### Conformance

Product Certifications	CUL Listed CE Industry Canada UL Listed VDE
------------------------	---------------------------------------------------------

## Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity

## Ordering and shipping details

GTIN	731304330363
Package weight(Lbs)	893.86 lb(US) (405.45 kg)

## Packing Units

Package 1 Height	85.28 in (216.6 cm)
Package 1 width	33.46 in (85 cm)
Package 1 Length	44.76 in (113.7 cm)
Number of Units in Package 3	1

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

## Contractual warranty

Warranty	1 year (parts only), 1 year on-site repair or replace with factory authorized Start-Up
----------	----------------------------------------------------------------------------------------