



### Overview

Presentation	Extends local access to your Multi-Platform Analog KVM console (AP5201, AP5202) up to 500 feet/152 meters.
Lead time	Usually in Stock

### Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Number of cables	1
Provided Equipment	Power adapter User Manual

### Physical

Color	Black
Height	1.61 in (4.1 cm)
Width	3.90 in (9.9 cm)
Depth	3.19 in (8.1 cm)
Net Weight	1.76 lb(US) (0.8 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Conformance

Product Certifications	CE TAA compliance
Standards	FCC Part 15 class A

### Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...85 %
Ambient Air Temperature for Storage	-4...122 °F (-20...50 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...85 %

### Ordering and shipping details

GTIN	731304225430
Package weight(Lbs)	2.01 lb(US) (0.91 kg)

## Packing Units

Package 1 Height	2.01 in (5.1 cm)
Package 1 width	5.00 in (12.7 cm)
Package 1 Length	6.50 in (16.5 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------