

RACSC112

InRow SC System 1 InRow SC, 1 NetShelter
SX Rack 600mm, with Front and Rear
Containment



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Main Input Voltage	200 V 208 V 220 V 230 V 240 V
Plug standard	NEMA L6-20P
Number of rack unit	42U
Number of cables	1
Provided Equipment	Installation guide

General

Compressor Type	Rotary
Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Refrigerant Charge	3 lb(US) (1.36 kg)
Air flow	1200 ft ³ /min (566.34 l/s)
Inrush current	56 A
Condensate Pump Capacity	1.3 Gal/hr(US) (0.00 m3/h)

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	35.43 in (90 cm)
Depth	58.15 in (147.7 cm)
Net Weight	825.04 lb(US) (374.23 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input power	2940 W
Input Frequency	60 Hz

Environmental

Acoustic level	70 dBA
----------------	--------

Communications & Management

Control panel	Multi-function LCD status and control console
---------------	---

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------