

Product data sheet

Specifications



Illuminated monolithic push button,
Harmony XB6E, square red flush,
16mm, latching, 24V DC, 2CO

XB6ECF4B2P

Main

| | |
|-------------------------------|---|
| Range of product | Harmony XB6E |
| Product or component type | Illuminated monolithic push-button |
| Device short name | XB6E |
| Bezel material | Plastic |
| Mounting diameter | 16 mm |
| Sale per indivisible quantity | 5 |
| Shape of signaling unit head | Square |
| Type of operator | latching |
| Operator profile | Red flush |
| Contacts type and composition | 2 C/O |
| Contact operation | Snap action |
| Connections - terminals | Faston connectors, connection size: 2.8 x 0.5 mm Soldered connectors |
| Contacts material | Gold-flashed silver |
| Light source | Integral LED |
| [Us] rated supply voltage | 24 V DC polarised |

Complementary

| | |
|---|--|
| Height | 18 mm |
| Width | 18 mm |
| Depth | 40 mm |
| Terminals description ISO n°1 | (23-24-21-22)OF (13-14-11-12)OF |
| Net weight | 0.006 kg |
| Overvoltage category | II conforming to IEC 60536 |
| Operating position | Any position |
| Marking | CE |
| Operating force | 1.3 N C/O changing electrical state |
| Mechanical durability | 250000 cycles |
| Short-circuit protection | 3 A cartridge fuse type gG |
| [Ith] conventional free air thermal current | 3 A |
| [Ui] rated insulation voltage | 250 V (pollution degree 2) conforming to IEC 60947-1 |

| | |
|---|---|
| [U _{imp}] rated impulse withstand voltage | 2.5 kV conforming to IEC 60947-1 |
| Electrical durability | 50000 cycles, DC-12, 1 A at 30 V conforming to IEC 60947-5-1 appendix C 50000 cycles, AC-12, 0.5 A at 125 V conforming to IEC 60947-5-1 appendix C 50000 cycles, AC-12, 0.5 A at 250 V conforming to IEC 60947-5-1 appendix C |
| Electrical reliability | $\lambda = 10\exp(-8)$ at 5 V and 1 mA with confidence level of 90 % conforming to IEC 60947-5-4 |
| Signalling type | Steady |
| Current consumption | 10 mA |
| Service life | 50000 h |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for storage | -40...70 °C |
| Ambient air temperature for operation | -10...55 °C |
| IP degree of protection | IP65 conforming to IEC 60529 |
| Standards | UL 508 JIS C 4520 CSA C22.2 No 14 JIS C 852 IEC 60947-5-1 IEC 60947-1 |
| Product certifications | CCC cURus |
| Vibration resistance | 1 mm (f= 5...55 Hz) conforming to IEC 60068-2-6 9 gn (f= 5...55 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 20 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |
| Electromagnetic compatibility | Electrostatic discharge immunity test - test level: 8 kV conforming to IEC 61000-4-2 |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.500 cm |
| Package 1 Width | 4.000 cm |
| Package 1 Length | 9.000 cm |
| Package 1 Weight | 12.400 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |
| Package 2 Height | 3.500 cm |
| Package 2 Width | 9.000 cm |
| Package 2 Length | 18.500 cm |
| Package 2 Weight | 62.000 g |
| Unit Type of Package 3 | S01 |
| Number of Units in Package 3 | 50 |
| Package 3 Height | 15.000 cm |
| Package 3 Width | 15.000 cm |
| Package 3 Length | 40.000 cm |

Package 3 Weight 775.000 g

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint **1**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

Use Again

Repack and remanufacture

End of life manual availability [End of Life Information](#)


Take-back **No**

WEEE Label **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**

Dimensions Drawings

Pushbutton

Square Head



(1) Anti-rotation plate (thickness: 0.6 mm / 0.02 in.)

(2) Seal (thickness: 0.5 mm / 0.01 in.)

e panel thickness: 0.5 mm (0.01 in.) \leq e \leq 6 mm (0.24 in.)

Mounting and Clearance

Panel Cut-Out and Mounting

Circular or Square Head

