

Product data sheet

Specifications



Complete pre wired monolithic tower light, Harmony XVC, plastic, red, 60mm, tube mounting, steady or flashing, buzzer, IP23, 100...240V AC

XVC6M15S

ⓘ To be discontinued

ⓘ To be discontinued on: May 31, 2026

Main

Range of product	Harmony XVC6
Product or component type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	1 illuminated unit
Sound signalling	Buzzer
Mounting diameter	60 mm
Component name	XVC
Light source	LED steady or flashing red
[Us] rated supply voltage	100...240 V
Supply circuit type	AC
Noise level	70...85 dB (continuous or intermittent tone) at 1 m

Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94-V0): top cover
Product mounting	On support tube, 22 mm
Cable cross section	0.83 mm ² 0.33 mm ²
AWG gauge	AWG 22 AWG 18
Cable length	450 mm
Marking	CE
[Uiimp] rated impulse withstand voltage	4 kV
Current consumption	60 mA
Fundamental frequency	2.23 kHz
Flashing frequency	1 Hz
Product weight	1.01 kg
Height	599.8 mm

Environment

Standards	IEC 60947-1 IEC 60947-5-1
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Electrical shock protection class	Class I conforming to IEC 61140
IP degree of protection	IP23 vertical surface installation conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.700 cm
Package 1 Width	8.700 cm
Package 1 Length	77.000 cm
Package 1 Weight	950.000 g
Unit Type of Package 2	P06
Number of Units in Package 2	10
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	18.000 kg

Contractual warranty

Warranty	18 months
-----------------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again


Repack and remanufacture

Take-back	No
-----------	----

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting**Dimensions**

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b1** dimension.




No. of illuminated units	b1 With buzzer (mm)	b1 With buzzer (in.)
1 stage	599.8	23.61
2 stages	639.8	25.19
3 stages	679.8	26.76
4 stages	719.8	28.34
5 stages	759.8	29.91

Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting



Technical Illustration

Dimensions

