

# Product data sheet

Specifications



Control station, Harmony eXLhoist, standard, XARS12D18W system with charger, shoulder belt, cable USB RJ45 and config software

XARSK12D18W

⚠ To be discontinued on: Mar 31, 2026

⚠ To be discontinued

## Main

Range of product	Harmony eXLhoist
Product or component type	Control station
Device short name	XARS
Control station type	Wireless
Product specific application	Hoisting applications Material handling
Number of channels	50
Control station application	Stop function: SIL 2 maximum (can reach PL d/category 3) conforming to IEC 62061 Stop function: SIL 2 maximum (can reach PL d/category 3) conforming to ISO 13849-1 Emergency stop function: SIL 3 maximum (can reach PL e/category 4) conforming to IEC 62061 Emergency stop function: SIL 3 maximum (can reach PL e/category 4) conforming to ISO 13849-1 Motion function: SIL 1 maximum (can reach PL c/category 1) conforming to IEC 62061 Motion function: SIL 1 maximum (can reach PL c/category 1) conforming to ISO 13849-1 Limiter protection function: SIL 1 maximum (can reach PL c/category 1) conforming to IEC 62061 Limiter protection function: SIL 1 maximum (can reach PL c/category 1) conforming to ISO 13849-1

## Complementary

Kit composition	Base station Configuration software Cable Remote control Shoulder belt
Operating distance	100 m in free air
cable entry	Cable gland
Communication network type	Wireless: bluetooth low energy
Transmission frequency	2.4 GHz

## Environment

Radio agreement	ARIB SRRC RSS ANATEL FCC ICASA
Relative humidity	0...95 % at -20...45 °C storage

<b>Electromagnetic compatibility</b>	Resistance to electrostatic discharge - test level: 4 kV class B (on contact) conforming to IEC 61000-4-2 Resistance to electrostatic discharge - test level: 8 kV class B (in air) conforming to IEC 61000-4-2 Resistance to radiated electromagnetic fields - test level: 10 V/m class B conforming to IEC 61000-4-3
--------------------------------------	--

<b>Standards</b>	IEC 60204-1 safety ISO 13849-1 safety IEC 62061 safety IEC 61508 safety ISO 13850 safety IEC 60204-32 hoisting applications ETSI EN 301 489-1 radio ETSI EN 301 489-3 radio ETSI EN 301 489-17 radio ETSI EN 300 440-2 radio ETSI EN 300 328 radio FCC part 15 radio RSS GEN issue 3 radio RSS 210 issue 8 radio ARIB STD-T81 radio
------------------	---

<b>Product certifications</b>	CE UL CSA C-Tick JIS KC EAC
-------------------------------	---

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	20.000 cm
<b>Package 1 Width</b>	29.000 cm
<b>Package 1 Length</b>	31.000 cm
<b>Package 1 Weight</b>	3.042 kg
<b>Unit Type of Package 2</b>	S04
<b>Number of Units in Package 2</b>	2
<b>Package 2 Height</b>	30.000 cm
<b>Package 2 Width</b>	40.000 cm
<b>Package 2 Length</b>	60.000 cm
<b>Package 2 Weight</b>	6.820 kg



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint	2145
----------------------------------	------

### Use Better

#### Materials and Substances

Packaging made with recycled cardboard	No
--	----

Packaging without single use plastic	No
--------------------------------------	----

<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
-----------------------------------	--

SCIP Number	6e438e59-42d1-4633-bfe2-cb5ef607659b
-------------	--------------------------------------

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
---------------------------	--

### Use Again

#### Repack and remanufacture

Take-back	No
-----------	----

WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------------	---

Image of product / Alternate images

Alternative

---







Image of product in real life situation

