

# Product data sheet

Specifications



socket equipped with LED and protection circuit, Harmony Electromechanical Relays, for RSL1 relays, spring terminals, 110V AC DC

RSLZRA3

## Main

Range of product	Harmony Electromechanical Relays
Device short name	RSLZ
Product or component type	Socket
Device presentation	Basic element
Product compatibility	Plug-in relay RSL with 1 C/O contact at 60 V DC
Contacts type and composition	1 C/O
[Ith] conventional free air thermal current	6 A
Switching voltage	110 V AC/DC
Rated operational voltage limits	88...126.5 V
[Ue] rated operational voltage	< 300 V AC

## Complementary

Group of product	RSL_SPRING_TERS_110
Shape of pin	Flat
Contact terminal arrangement	Separate
Connections - terminals	Spring terminals, 1 x 0.2...1 x 1.5 mm <sup>2</sup> (AWG 24...AWG 16) flexible with cable end Spring terminals, 1 x 0.2...1 x 1.5 mm <sup>2</sup> (AWG 24...AWG 16) solid without cable end
Compatibility code	RSLZ
Clamping force	10...40 N
Fixing mode	Plastic compression spring (35 mm symmetrical DIN rail)
[Uimp] rated impulse withstand voltage	3.6 kV
Overvoltage category	III
Pollution degree	3
Sale per indivisible quantity	10
CAD overall width	6.2 mm
CAD overall height	78.6 mm
CAD overall depth	101 mm
Product weight	0.023 kg

## Environment

IP degree of protection	IP20 conforming to IEC 60529
-------------------------	------------------------------

<b>Standards</b>	IEC 61984 UL 508
<b>Product certifications</b>	CSA GOST
<b>Marking</b>	CE
<b>Ambient air temperature for storage</b>	-40...85 °C
<b>Ambient air temperature for operation</b>	-40...55 °C

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	0.600 cm
<b>Package 1 Width</b>	8.500 cm
<b>Package 1 Length</b>	10.800 cm
<b>Package 1 Weight</b>	24.000 g
<b>Unit Type of Package 2</b>	BB1
<b>Number of Units in Package 2</b>	10
<b>Package 2 Height</b>	7.000 cm
<b>Package 2 Width</b>	8.800 cm
<b>Package 2 Length</b>	10.800 cm
<b>Package 2 Weight</b>	265.000 g
<b>Unit Type of Package 3</b>	S03
<b>Number of Units in Package 3</b>	300
<b>Package 3 Height</b>	30.000 cm
<b>Package 3 Width</b>	30.000 cm
<b>Package 3 Length</b>	40.000 cm
<b>Package 3 Weight</b>	8.663 kg

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint

1

## Use Better

### Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation

[REACH Declaration](#)

California proposition 65

**WARNING:** This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Use Again


### Repack and remanufacture

Take-back


No

## Dimensions Drawings

## Dimensions




## Connections and Schema

Wiring Diagram

(1) Protection circuit

**Example of RSLZ2 Bus Jumper Mounting on Sockets**

Side View



(1) A1

(2) A2

(3) Bus jumper polarity A1

(4) Bus jumper polarity A2

## Technical Illustration

## Dimensions




Image of product / Alternate images

Alternative

---

