

Product data sheet

Specifications



Light block, Harmony XB4, Harmony XB5, for head 22mm, universal LED, 24V AC DC, compact push in terminals

ZBVB15

Main

| | |
|-------------------------------|--|
| Range of product | Harmony XB4 Harmony XB5 |
| Product or component type | Light block |
| Device short name | ZBV |
| Sale per indivisible quantity | 5 |
| Connections - terminals | Push-in, <= 2 x 1.5 mm ² with wire end ferrule conforming to IEC 60947-1 Push-in, >= 1 x 0.34 mm ² without wire end ferrule conforming to IEC 60947-1 |
| Signalling type | Steady |
| Light source | Universal LED |
| Bulb base | Integral LED |
| Light block supply | Direct |
| Light source colour | White |
| [Us] rated supply voltage | 24 V AC/DC at 50/60 Hz |

Complementary

| | |
|-----------------------|--------------------------------------|
| CAD overall width | 35.6 mm |
| CAD overall height | 14.8 mm |
| CAD overall depth | 9.8 mm |
| Product weight | 0.005 kg |
| Supply voltage limits | 20.4...26.4 V DC 20.4...26.4 V AC |
| Current consumption | 15 mA |
| Service life | 100000 h at rated voltage and 25 °C |
| Surge withstand | 1 kV conforming to IEC 61000-4-5 |
| Mounting of block | Front mounting |
| Device presentation | Basic element |

Environment

| | |
|---------------------------------------|------------------------------|
| Protective treatment | TH |
| Ambient air temperature for storage | -40...70 °C |
| Ambient air temperature for operation | -40...70 °C |
| IP degree of protection | IP20 conforming to IEC 60529 |

| | |
|--|---|
| Standards | IEC 60947-1 IEC 60947-5-1 IEC 60947-5-4 IEC 60947-5-5 UL 60947-1 UL 60947-5-1 UL 60947-5-5 UL 1059 UL 486E CSA C22.2 No 60947-1 CSA C22.2 No 60947-5-1 CSA C22.2 No 158 CSA C22.2 No 65 IACS E10 |
| Product certifications | EAC IECCE CB Scheme CCC UL CSA |
| Resistance to fast transients | 2 kV conforming to IEC 61000-4-4 |
| Resistance to electromagnetic fields | 10 V/m conforming to IEC 61000-4-3 |
| Resistance to electrostatic discharge | 4 kV on contact (on metal parts) conforming to IEC 61000-4-2 8 kV in free air (in insulating parts) conforming to IEC 61000-4-2 |
| Electromagnetic emission | Class B conforming to IEC 55011 |
| [Us] rated supply voltage | 24 V |

Packing Units

| | |
|-------------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4.3 cm |
| Package 1 Width | 5.2 cm |
| Package 1 Length | 5.4 cm |
| Package 1 Weight | 5 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |
| Package 2 Height | 4.3 cm |
| Package 2 Width | 5.2 cm |
| Package 2 Length | 5.4 cm |
| Package 2 Weight | 30 g |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 800 |
| Package 3 Height | 30 cm |
| Package 3 Width | 30 cm |
| Package 3 Length | 40 cm |
| Package 3 Weight | 5.241 kg |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty | 18 months |
|-----------------|-----------|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint 5

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard No

Packaging without single use plastic No

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

SCIP Number E148b25a-d37b-4237-bc1f-74823046728d

California proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

Use Again

Repack and remanufacture

End of life manual availability [End of Life Information](#)


Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins


Dimensions Drawings

Dimensions

with ZB5AZ009 Fixing Collar




with ZB4BZ009 Fixing Collar




Mounting and Clearance

Mounting

Mounting and Unmounting



Panel cut-out Dimension





Connections and Schema

Wiring

Wiring and Unwiring




| | |
|------------------------|-----------------------|
| mm in. | 8 0.32 |
| mm ² AWG | 0.34...1.5 22...16 |




| | | | |
|------------------------|-----------------------|---------------------|-----------------------|
| mm in. | 8 0.32 | 8 0.32 | 8 0.32 |
| mm ² AWG | 0.34...1.5 22...16 | 0.34...1 22...18 | 0.34...1.5 22...16 |

(1) Max
1.9 mm
0.07 in.
2.4 mm
0.09 in.



Technical Illustration

Dimensions



Technical Illustration

Wiring diagram




Image of product / Alternate images

Alternative





