

# Product data sheet

Specifications



ClimaSys forced vent. IP54, 262m3/h, 24V DC, with outlet grille and filter G2

NSYCVF300M24DPF

## Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of filter	Standard
Flow rate	Free flow rate with standard filter: 262 m3/h
[Us] rated supply voltage	12...30 V
Input voltage	24 V DC
Certification	CSA

## Complementary

Absorbed power	13 W
[In] rated current	0.53 A
Noise level < at	60...68 dB
Bearing type	Ball
Height	External: 268 mm
Width	External: 248 mm
Depth	External : 103.4 mm
Cut-out dimensions	223 x 223 mm
Product weight	1.1 kg
Material	Outlet grille: injected thermoplastic (ASA PC)
Colour	Outlet grille: grey (RAL 7035)
Ambient air temperature for operation	-10...70 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	158 Pa flow rate 0 m³/h
Connections - terminals	Cable
IP degree of protection	IP54
Device composition	1 axial motor 2 protective grille: on the front and rear surfaces 1 filter: front of axial motor 1 outlet grille: front 1 cut-out template 1 power cord

---

<b>Condition of use</b>	Overfrequent filter replacement should be avoided Outside temperature must be 5 °C lower than inside temperature Flow rates depends on the work point, see ProClima software Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean
-------------------------	---

## Packing Units

---

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	18.500 cm
<b>Package 1 Width</b>	25.000 cm
<b>Package 1 Length</b>	27.500 cm
<b>Package 1 Weight</b>	1.360 kg
<b>Unit Type of Package 2</b>	CAR
<b>Number of Units in Package 2</b>	4
<b>Package 2 Height</b>	28.000 cm
<b>Package 2 Width</b>	41.000 cm
<b>Package 2 Length</b>	59.000 cm
<b>Package 2 Weight</b>	6.460 kg
<b>Unit Type of Package 3</b>	P12
<b>Number of Units in Package 3</b>	64
<b>Package 3 Height</b>	125.000 cm
<b>Package 3 Width</b>	80.000 cm
<b>Package 3 Length</b>	120.000 cm
<b>Package 3 Weight</b>	114.000 kg

## Contractual warranty

---

<b>Warranty</b>	18 months
-----------------	-----------



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint **14**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **No**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant with Exemptions**

SCIP Number **61d9d3f3-5a49-48f8-8056-1a5ad0ad4c76**

REACH Regulation [REACH Declaration](#)

## Use Again

### Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back **No**

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins