

# Product data sheet

Specifications



## thermal overload relays, TeSys Deca, 90...150A, class 10

LR9D5369

**To be discontinued on:** Dec 31, 2026

**To be discontinued**

### Main

Range	TeSys
Product name	TeSys LRD TeSys Deca
Product or component type	Electronic thermal overload relay
Device short name	LR9D
Relay application	Motor protection
Product compatibility	NSX circuit breaker LC1D150 LC1D115
Network type	AC
Thermal overload class	Class 10 conforming to IEC 60947-4-1
Signalling function	Alarm
Thermal protection adjustment range	90...150 A
[Ui] rated insulation voltage	Power circuit: 1000 V conforming to IEC 60947-4-1 Power circuit: 600 V conforming to CSA Power circuit: 600 V conforming to UL

### Complementary

Network frequency	50...60 Hz
[Us] rated supply voltage	24 V DC
Supply voltage limits	17...32 V
Mounting support	Under contactor Rail
Tripping threshold	1.05 +/- 0.06 In alarm conforming to IEC 60947-4-1 1.12 +/- 0.06 In de-energisation conforming to IEC 60947-4-1
Auxiliary contact composition	1 NO + 1 NC
[Ith] conventional free air thermal current	5 A for signalling circuit
[Ue] rated operational voltage	690 V AC 0...400 Hz for power circuit conforming to IEC 60947-4-1
Associated fuse rating	4 A gG for signalling circuit 4 A BS for signalling circuit
[Uiimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-1
Phase failure sensitivity	Tripping in 4 s +/- 20 % conforming to IEC 60947-4-1
Control type	Red push-button: stop Blue push-button: reset

Temperature compensation	-20...60 °C
Switching capacity in mA	0...150 mA
Maximum voltage drop	<2.5 V closed state
Connections - terminals	Power circuit: bars Control circuit: screw clamp terminals 1 cable(s) 0.5...1.5 mm <sup>2</sup> flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 0.5...1.5 mm <sup>2</sup> flexible without cable end Alarm circuit: screw clamp terminals 1 cable(s) 0.5...1.5 mm <sup>2</sup> flexible without cable end
Tightening torque	Alarm circuit: 0.45 N.m - on screw clamp terminals Power circuit: 18 N.m - on bars M8 Control circuit: 1.2 N.m - on screw clamp terminals
Height	118 mm
Width	115 mm
Depth	125 mm
Product weight	0.885 kg

## Environment

Climatic withstand	conforming to IACS E10
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...60 °C without derating conforming to IEC 60947-4-1
Ambient air temperature for storage	-60...70 °C
Operating altitude	<= 2000 m without derating
Mechanical robustness	Vibrations: 2 Gn, 5...300 Hz conforming to IEC 60068-2-6 Shocks: 13 Gn for 11 ms conforming to IEC 60068-2-7
Dielectric strength	1.89 kV at 50 Hz conforming to IEC 60947-1
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5
Product certifications	UL CSA CCC UKCA

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.000 cm
Package 1 Width	16.000 cm
Package 1 Length	13.000 cm
Package 1 Weight	920.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	30.000 cm

Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	11.880 kg
Unit Type of Package 3	P06
Number of Units in Package 3	48
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	56.804 kg

## Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint	133
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant with Exemptions
SCIP Number	D5a17874-1166-4927-b008-33d15e304a41
California proposition 65	<b>WARNING:</b> This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="#">www.P65Warnings.ca.gov</a>
PVC free	Yes

## Use Again

### Repack and remanufacture

End of life manual availability	<a href="#">End of Life Information</a>
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins