

Product data sheet

Specifications



Short-circuit signalling contact block, TeSys Deca Frame 2 & 3, 1C/O, side, for GV2/GV3(except GV3ME)

GVAM11

Main

Range	TeSys TeSys Deca
Device short name	GVAM
Product or component type	Auxiliary contact block
Product compatibility	GV2L GV2ME GV2RT GV3L GV2P GV3P GV2LE
Mounting location	Left side
Auxiliary contacts operation	Short-circuit signal 1 C/O
Pole contact composition	1 C/O

Complementary

[Ui] rated insulation voltage	690 V conforming to IEC 60947-1 300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14
[Ue] rated operational voltage	24...240 V AC 24...60 V DC
[ith] conventional free air thermal current	2.5 A for fault signalling
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Protection type	GB2CB... circuit breaker GG fuse 10 A
Rated operational power in VA	36 VA at 24 V AC-14 - electrical durability: 1000 cycles at 1.5 A 48 VA at 48 V AC-14 - electrical durability: 1000 cycles at 1 A 72 VA at 110...127 V AC-14 - electrical durability: 1000 cycles at 0.5 A 72 VA at 230...240 V AC-14 - electrical durability: 1000 cycles at 0.3 A
Rated operational power in W	120 W at 240 V DC-13 - electrical durability: 100000 cycles 140 W at 110 V DC-13 - electrical durability: 100000 cycles 140 W at 24 V DC-13 - electrical durability: 100000 cycles 180 W at 60 V DC-13 - electrical durability: 100000 cycles 240 W at 48 V DC-13 - electrical durability: 100000 cycles 15 W at 48 V DC-13 - electrical durability: 1000 cycles 24 W at 24 V DC-13 - electrical durability: 1000 cycles 9 W at 60 V DC-13 - electrical durability: 1000 cycles
Tightening torque	1.4 N.m - on screw clamp terminals
Height	89 mm

Width	9.3 mm
Depth	66 mm
Product weight	0.055 kg
Colour	Dark grey

Environment

Environmental characteristic	Normal environment
Product certifications	UKCA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	7.0 cm
Package 1 Length	9.0 cm
Package 1 Weight	39 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	10.0 cm
Package 2 Width	10.5 cm
Package 2 Length	15.3 cm
Package 2 Weight	440 g
Unit Type of Package 3	S02
Number of Units in Package 3	60
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2.944 kg

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint 1

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Compliant

California proposition 65 WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

End of life manual availability [End of Life Information](#)


Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Connections and Schema

Short-Circuit Signalling Contacts

GVAM11



Technical Illustration

Assembly's dimensions

