

Product data sheet

Specifications



Communication module, TeSys Ultra, 24VDC, Modbus RTU, front side

LULC033

Main

Range	TeSys
Device short name	LUL
Product or component type	Communication module
Product compatibility	LUCL LUCC LUCB LUCM LUCA LUCD
Device application	Communication
Range compatibility	TeSys TeSys U LUB non reversing power base TeSys TeSys U LU2B reversing power base

Complementary

main function available	Communication module
Mounting mode	Plug-in
Mounting location	Front side
Physical interface	RS485 multidrop
Bus type	Modbus
Cable connector type	RJ45 front panel
Communication port protocol	Modbus RTU
Addressing	0...31
Transmission rate	19200 bit/s
Return time	30 ms
Number of inputs	2
Logic input	Positive at 24 V DC - 7 mA
Response time	10 ms +/- 30 % change to state 0 10 ms +/- 30 % change to state 1
Input type	Resistive
Number of outputs	2 dedicated to starter-controller coil operation 1
[Us] rated supply voltage	24 V DC
Output current	<= 500 mA
Protection type	GG fuse 1 A
Switching current capacity	0.5 mA at 24 V

Local signalling	3 LEDs front panel
Connection pitch	3.81 mm
Connections - terminals	Screw clamp terminals 1 cable(s) 0.14...1 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 0.14...1 mm ² rigid without cable end Screw clamp terminals 1 cable(s) 0.25...0.5 mm ² flexible with cable end Screw clamp terminals 1 cable(s) 0.25...1 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.14...0.5 mm ² rigid without cable end Screw clamp terminals 2 cable(s) 0.14...0.75 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 0.25...0.34 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.5 mm ² flexible with cable end
Associated cable type	AWG 26...AWG 16
Tightening torque	0.2...0.25 N.m2.5 mm
Product weight	0.08 kg

Environment

Ambient air temperature for operation	-25...55 °C
IP degree of protection	IP20 conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	11.3 cm
Package 1 Length	4.9 cm
Package 1 Weight	85.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	35
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.293 kg

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	E383808a-7832-4e0a-8697-e499929809d4
Halogen-free status	Halogen free plastic parts product

Use Again

Repack and remanufacture

End of life manual availability	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins