

# Product data sheet

Specifications



## Auxiliary contact, TeSys GV4, 690VAC, 1 NO/NC

GV4AE11

### Main

Range	TeSys
Device short name	GV4AE
Product or component type	Auxiliary contact
Device application	Signalling
Range compatibility	TeSys TeSys GV4 TeSys TeSys BV4
Auxiliary contact composition	1 NO/NC
[Ue] rated operational voltage	<= 690 V
[Ith] conventional free air thermal current	5 A conforming to IEC 60947-5-1 5 A conforming to CSA C22.2 No 14 5 A conforming to UL 508
Mounting mode	Internal mounting

### Complementary

[Ui] rated insulation voltage	690 V conforming to IEC 60947-1
[Ie] rated operational current	5 A <= 690 V AC-12 conforming to IEC 60947-5-1 5 A <= 48 V AC-15 conforming to IEC 60947-5-1 4 A 110/127 V AC-15 conforming to IEC 60947-5-1 3 A 220/240 V AC-15 conforming to IEC 60947-5-1 2.5 A 380...440 V AC-15 conforming to IEC 60947-5-1 0.11 A 660/690 V AC-15 conforming to IEC 60947-5-1 5 A <= 24 V DC-12 conforming to IEC 60947-5-1 2.5 A 48 V DC-12 conforming to IEC 60947-5-1 0.6 A 110/127 V DC-12 conforming to IEC 60947-5-1 0.3 A 250 V DC-12 conforming to IEC 60947-5-1 2.5 A <= 24 V DC-12 conforming to IEC 60947-5-1 1.2 A 48 V DC-12 conforming to IEC 60947-5-1 0.35 A 110/127 V DC-12 conforming to IEC 60947-5-1 0.05 A 250 V DC-12 conforming to IEC 60947-5-1 1 A <= 24 V DC-12 conforming to IEC 60947-5-1 0.2 A 48 V DC-12 conforming to IEC 60947-5-1 0.05 A 110/127 V DC-12 conforming to IEC 60947-5-1 0.03 A 250 V DC-12 conforming to IEC 60947-5-1
Rated power in VA	120 VA AC-12 at 24 V conforming to IEC 60947-5-1 240 VA AC-12 at 48 V conforming to IEC 60947-5-1 635 VA AC-12 at 110/127 V conforming to IEC 60947-5-1 1200 VA AC-12 at 230/240 V conforming to IEC 60947-5-1 2200 VA AC-12 at 380/440 V conforming to IEC 60947-5-1 3450 VA AC-12 at 660/690 V conforming to IEC 60947-5-1
Rated power in W	DC-12: 120 W 24 V conforming to IEC 60947-5-1 DC-12: 120 W 48 V conforming to IEC 60947-5-1 DC-12: 66 W 110 V conforming to IEC 60947-5-1 DC-12: 75 W 250 V conforming to IEC 60947-5-1
Associated fuse rating	5 A gG at 690 V conforming to IEC 60947-5-1
Minimum switching current	2 mA

Minimum switching voltage	17 V
Mechanical durability	40000 cycles
Connections - terminals	Spring terminals 1 0.5...1.5 mm <sup>2</sup> - cable stiffness: flexible without cable end
Wire stripping length	8 mm

## Environment

Quantity per set	Set of 1
------------------	----------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	8.000 cm
Package 1 Length	11.000 cm
Package 1 Weight	24.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.000 cm
Package 2 Width	16.000 cm
Package 2 Length	27.000 cm
Package 2 Weight	251.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	220
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.353 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant
California proposition 65	<b>WARNING:</b> This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>
Halogen-free status	Halogen free plastic parts product
PVC free	Yes

## Use Again

### Repack and remanufacture

End of life manual availability	<a href="#">No need of specific recycling operations</a>
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins