

Product data sheet

Specifications



Modicon M172 Display Color TouchScreen, Temperature, Humidity, built-in sensors

TM172DCLWTHP

Main

| | |
|---------------------------|-------------------|
| Range of product | Modicon M171/M172 |
| Product or component type | Display module |
| Supply | External source |

Complementary

| | |
|---------------------------|--|
| Display type | LCD display Colour touchscreen |
| Display resolution | 320 x 240 pixels |
| Colour | White |
| [Us] rated supply voltage | 24 V AC/DC |
| Power consumption in W | 3.2 VA 1.3 W |
| Analogue input type | NTC 10k type 2 temperature probe - 40...50 °C +/- 0.1 °C NTC 10k temperature probe at 21 °C +/- 0.5 °C Humidity probe 10...90 % without condensation 10...20 % +/- 10 % Humidity probe 10...90 % without condensation 20...80 % +/- 5 % Humidity probe 10...90 % without condensation 80...90 % +/- 10 % |
| Product compatibility | Logic controller M171 Logic controller M172 |
| Height | 120 mm |
| Width | 86 mm |
| Depth | 25 mm |
| Product weight | 0.34 kg |

Environment

| | |
|------------|--|
| Directives | 2014/30/EU - electromagnetic compatibility 2014/35/EU - low voltage directive |
|------------|--|

| | |
|-----------|--|
| Standards | IEC 60950-1 EN 55024 EN 55032 CSA C22.2 No 24 UL 873 |
|-----------|--|

| | |
|------------------------|----------------------------|
| Product certifications | EAC CE RCM cTUVus |
|------------------------|----------------------------|

| | |
|---------------------------------------|-----------|
| Ambient air temperature for operation | 0...50 °C |
|---------------------------------------|-----------|

| | |
|-------------------------------------|-------------|
| Ambient air temperature for storage | -30...50 °C |
|-------------------------------------|-------------|

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.0 cm |
| Package 1 Width | 10.6 cm |
| Package 1 Length | 15.5 cm |
| Package 1 Weight | 226.0 g |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 11 |
| Package 2 Height | 15.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 2.858 kg |



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

| | |
|--|--|
| Packaging made with recycled cardboard | No |
| Packaging without single use plastic | No |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| SCIP Number | Efa76fc9-0353-46a9-be6e-1c1736225165 |
| REACH Regulation | REACH Declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Use Again

Repack and remanufacture

| | |
|---------------------------------|---|
| End of life manual availability | End of Life Information |
| Take-back | No |
| WEEE Label | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |