

Product data sheet

Specifications



Add-on contact block, TeSys Deca
Frame 2/3, 1NO+1NO, side, spring
terminal, for GV2/GV3(except
GV3ME)

GVAN113

Main

Range	TeSys TeSys Deca
Device short name	GVAN
Product or component type	Auxiliary contact block
Product compatibility	GV3P GV2RT GV2P GV3L GV2ME GV2L GV2LE
Mounting location	Left side
Pole contact composition	1 NO + 1 NC

Complementary

[Ui] rated insulation voltage	600 V conforming to UL 508 690 V conforming to IEC 60947-1 600 V conforming to CSA C22.2 No 14
[Ue] rated operational voltage	48...690 V AC 24...240 V DC
[Ith] conventional free air thermal current	6 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Protection type	GB2CB... circuit breaker GG fuse 10 A
Rated operational power in VA	300 VA at 48 V AC-15 - electrical durability: 100000 cycles 414 VA at 690 V AC-15 - electrical durability: 100000 cycles 500 VA at 110...127 V AC-15 - electrical durability: 100000 cycles 500 VA at 500 V AC-15 - electrical durability: 100000 cycles 650 VA at 440 V AC-15 - electrical durability: 100000 cycles 720 VA at 230...240 V AC-15 - electrical durability: 100000 cycles 850 VA at 380...415 V AC-15 - electrical durability: 100000 cycles
Rated operational power in W	120 W at 240 V DC-13 - electrical durability: 100000 cycles 140 W at 110 V DC-13 - electrical durability: 100000 cycles 140 W at 24 V DC-13 - electrical durability: 100000 cycles 180 W at 60 V DC-13 - electrical durability: 100000 cycles 240 W at 48 V DC-13 - electrical durability: 100000 cycles
Height	89 mm
Width	9.3 mm
Depth	66 mm

Colour	Dark grey
--------	-----------

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Product certifications	UKCA
------------------------	------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	1.0 cm
------------------	--------

Package 1 Width	6.5 cm
-----------------	--------

Package 1 Length	9.0 cm
------------------	--------

Package 1 Weight	25.0 g
------------------	--------

Unit Type of Package 2	BB1
------------------------	-----

Number of Units in Package 2	10
------------------------------	----

Package 2 Height	9.8 cm
------------------	--------

Package 2 Width	10.0 cm
-----------------	---------

Package 2 Length	15.3 cm
------------------	---------

Package 2 Weight	500.0 g
------------------	---------

Unit Type of Package 3	S02
------------------------	-----

Number of Units in Package 3	60
------------------------------	----

Package 3 Height	15.0 cm
------------------	---------

Package 3 Width	30.0 cm
-----------------	---------

Package 3 Length	40.0 cm
------------------	---------

Package 3 Weight	3.325 kg
------------------	----------

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint 1

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Compliant

California proposition 65 WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Assembly's dimensions

