

Product data sheet

Specifications



Auxiliary contacts, TeSys GS, 1 NO, early break, front mounting, for GS2 with front/side handle

GS1AM110

Main

Range of product	TeSys
Device short name	GS1AM
Product or component type	Auxiliary contact
Contact application	O, I and test position signalling
Range compatibility	TeSys TeSys GS fuse-switch disconnecter FuPact FuPacT GS fuse-switch disconnecter
Contacts type and composition	1 NO
Contact operation	Early-break
[I _{th}] conventional free air thermal current	10 A (at 40 °C)
[I _e] rated operational current	6 A at 120 V AC-15 3 A at 240 V AC-15 1.8 A at 400 V AC-15 1.5 A at 480 V AC-15 2.8 A at 24 V DC-13 1.4 A at 48 V DC-13 0.55 A at 125 V DC-13 0.27 A at 250 V DC-13 0.15 A at 400 V DC-13

Complementary

Mechanical durability	5 Mcycles
Electrical durability	1 Mcycles AC-15
switch rated current	30 A 32 A 50 A 60 A 63 A 100 A 125 A 160 A 200 A 250 A 315 A 400 A 600 A 630 A 800 A 1250 A
Fuse type	NFC DIN BS CC J
Type of operating handle	External frontal External right side External left side

Mounting location	Front face
-------------------	------------

Product weight	0.015 kg
----------------	----------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	9 cm
------------------	------

Package 1 Width	8 cm
-----------------	------

Package 1 Length	2 cm
------------------	------

Package 1 Weight	13 g
------------------	------

Unit Type of Package 2	S01
------------------------	-----

Number of Units in Package 2	40
------------------------------	----

Package 2 Height	15 cm
------------------	-------

Package 2 Width	15 cm
-----------------	-------

Package 2 Length	40 cm
------------------	-------

Package 2 Weight	707 g
------------------	-------

Contractual warranty

Warranty	18 months
----------	-----------


Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.



[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Assembly's dimensions

