

# Product data sheet

Specifications



## Miniature circuit breaker (MCB), Multi9 C60H, 3P, 16A, C curve, 15kA (IEC/EN 60947-2)

M9F14316

### Main

Range	Multi9
Product name	Multi9 C60
Product or component type	Miniature circuit-breaker
Device short name	C60H
Device application	Distribution
Poles description	3P
Number of protected poles	3
[In] rated current	16 A at 50 °C conforming to EN/IEC 60947-2
Network type	AC DC
Network frequency	50/60 Hz
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	40 kA Icu at <= 125 V DC conforming to EN/IEC 60947-2 30 kA Icu at 240 V AC 50/60 Hz between phases conforming to EN/IEC 60947-2 15 kA Icu at 415 V AC 50/60 Hz between phases conforming to EN/IEC 60947-2 10 kA Icu at 440 V AC 50/60 Hz between phases conforming to EN/IEC 60947-2
Utilisation category	Category A conforming to EN/IEC 60947-2
Standards	EN/IEC 60947-2
Product certifications	EAC CCC

### Complementary

[Ue] rated operational voltage	240 V AC 50/60 Hz between phases 415 V AC 50/60 Hz between phases 440 V AC 50/60 Hz between phases <= 125 V DC
Magnetic tripping limit	8.5 x In +/- 20 % AC 12 x In +/- 20 % DC
[Ics] rated service breaking capacity	15 kA 50 % conforming to EN/IEC 60947-2 - 240 V AC 50/60 Hz 7.5 kA 50 % conforming to EN/IEC 60947-2 - 415 V AC 50/60 Hz 5 kA 50 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 40 kA 100 % conforming to EN/IEC 60947-2 - <= 125 V DC
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Contact position indicator	Yes

<b>Control type</b>	Toggle
<b>Local signalling</b>	ON/OFF indication
<b>Mounting mode</b>	Clip-on
<b>Mounting support</b>	DIN rail
<b>9 mm pitches</b>	6
<b>Height</b>	81 mm
<b>Width</b>	54 mm
<b>Depth</b>	72 mm
<b>Product weight</b>	0.36 kg
<b>Colour</b>	Grey
<b>Mechanical durability</b>	20000 cycles
<b>Electrical durability</b>	10000 cycles
<b>Provision for padlocking</b>	Padlockable
<b>Connections - terminals</b>	Tunnel type terminal (top or bottom)1...25 mm <sup>2</sup> - rigid Tunnel type terminal (top or bottom)1...25 mm <sup>2</sup> - flexible Tunnel type terminal (top or bottom)1...25 mm <sup>2</sup> - flexible with ferrule
<b>Wire stripping length</b>	14 mm for top or bottom connection
<b>Tightening torque</b>	2 N.m top or bottom
<b>Earth-leakage protection</b>	Separate block

## Environment

<b>IP degree of protection</b>	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
<b>Pollution degree</b>	3 conforming to EN/IEC 60947-2
<b>Overvoltage category</b>	IV
<b>Tropicalisation</b>	2 conforming to IEC 60068-1
<b>Relative humidity</b>	95 % at 55 °C
<b>Ambient air temperature for operation</b>	-30...70 °C
<b>Ambient air temperature for storage</b>	-40...80 °C

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	7.500 cm
<b>Package 1 Width</b>	5.400 cm
<b>Package 1 Length</b>	8.500 cm
<b>Package 1 Weight</b>	330.000 g
<b>Unit Type of Package 2</b>	BB1
<b>Number of Units in Package 2</b>	4
<b>Package 2 Height</b>	7.700 cm
<b>Package 2 Width</b>	9.000 cm
<b>Package 2 Length</b>	22.700 cm

<b>Package 2 Weight</b>	1.359 kg
<b>Unit Type of Package 3</b>	S03
<b>Number of Units in Package 3</b>	24
<b>Package 3 Height</b>	30.000 cm
<b>Package 3 Width</b>	30.000 cm
<b>Package 3 Length</b>	40.000 cm
<b>Package 3 Weight</b>	8.670 kg



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint 46

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Compliant

SCIP Number 40a4e715-7fff-45ff-88bf-38212f6a80a5

REACH Regulation [REACH Declaration](#)

California proposition 65 **WARNING: This product can expose you to chemicals including: DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)**

## Use Again

### Repack and remanufacture

End of life manual availability No need of specific recycling operations

Take-back No

WEEE Label  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

---

