

Product data sheet

Characteristics

LA1LC072F

TeSys Integral - undervoltage trip - 110 V AC
50 Hz - without time delay

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Device short name	LA1LC
Product or component type	Undervoltage trip
Product compatibility	LD4 LD5
Range compatibility	TeSys Integral contactor breaker

Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 110...120 V AC 60 Hz
Time delay	Without time delay
Voltage release type	Undervoltage release Instantaneous
Control circuit voltage limits	0.8...1.1 Uc
Threshold tripping voltage	0.35...0.7 Uc
Inrush power in VA	8 VA AC
Hold-in power consumption in VA	4 VA AC
Quantity per set	Set of 10
Product weight	0.33 lb(US) (0.15 kg)

Ordering and shipping details

Category	22384 - STARTERS,INTEGRAL,ACCESS
Discount Schedule	I11
GTIN	00785901223764
Nbr. of units in pkg.	1
Package weight(Lbs)	0.3400000000000002
Returnability	N
Country of origin	CZ

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Styrene, which is known to the State of California to cause cancer.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.