

Main

Range	TeSys
Product or Component Type	Fault discrimination device
Range compatibility	TeSys GV7

Complementary

Function Available	Differentiation of thermal overload and magnetic fault
Mounting Location	Inside of the front panel
Auxiliary contacts operation	Fault signal
[Ue] rated operational voltage	24 V DC control circuit 72 V DC control circuit 24 V AC 50/60 Hz control circuit 48 V AC 50/60 Hz control circuit
Net Weight	0.22 lb(US) (0.1 kg)
Quantity per Set	Set of 10


Ordering and shipping details

Category	22366-MAN STR PROTECTORS-GV1/GV3
Discount Schedule	I11
GTIN	3389110567281
Nbr. of units in pkg.	1
Package weight(Lbs)	1.27 oz (36.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	1.97 in (5 cm)
Package 1 Length	2.05 in (5.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes


RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------


Electric Trips

GV7AD111, AD112




Recommended Application Schemes GV7AD111, AD112

Fault indication



Associated components
KA1: CA2KN or CADN

Contactor opening on overload



Associated components KA1: CAD + LAD6K10 or RHKKM1: LC1 D or LC1 F
KA1: CAD + LAD6K10 or RHK
KM1: LC1 D or LC1 F