

Product data sheet

Specifications



TeSys Deca thermal overload relays - 48...65 A - class 20

LRD365L

Product availability: Stock - Normally stocked in distribution facility

Main

Range	TeSys TeSys Deca
Product name	TeSys LRD TeSys Deca
Product or Component Type	Differential thermal overload relay
Device short name	LRD
Relay application	Motor protection
Product Compatibility	LC1D50A LC1D65A
Network type	DC AC
Thermal overload class	Class 20 IEC 60947-4-1
Thermal protection adjustment range	48...65 A
[Ui] rated insulation voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 690 V IEC 60947-4-1

Complementary

Network Frequency	0...400 Hz
Mounting support	Plate, with specific accessories Rail, with specific accessories Under contactor
Tripping threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
Auxiliary contact composition	1 NO + 1 NC
[Ith] conventional free air thermal current	5 A signalling circuit
Permissible current	3 A 120 V AC-15 signalling circuit 0.22 A 125 V DC-13 signalling circuit
[Ue] rated operational voltage	690 V AC 0...400 Hz power circuit IEC 60947-4-1
Associated fuse rating	4 A gG for signalling circuit 4 A BS for signalling circuit
[Uiimp] rated impulse withstand voltage	6 kV
Phase failure sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control type	Red push-button stop Blue push-button reset
Temperature compensation	-4...140 °F (-20...60 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Connections - terminals	Control circuit screw clamp terminals 2 0.002...0.004 in ² (1...2.5 mm ²) flexible without cable end Control circuit screw clamp terminals 2 0.002...0.004 in ² (1...2.5 mm ²) flexible with cable end Control circuit screw clamp terminals 2 0.002...0.004 in ² (1...2.5 mm ²) solid without cable end Power circuit EverLink BTR screw connectors 1 0.002...0.05 in ² (1...35 mm ²) flexible without cable end Power circuit EverLink BTR screw connectors 1 0.002...0.05 in ² (1...35 mm ²) flexible with cable end Power circuit EverLink BTR screw connectors 1 0.002...0.05 in ² (1...35 mm ²) solid without cable end
Tightening torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 44.3 lbf.in (5 N.m) EverLink BTR screw connectors
Height	2.8 in (70 mm)
Width	2.2 in (55 mm)
Depth	4.8 in (123 mm)
Product Weight	0.827 lb(US) (0.375 kg)

Environment

Climatic withstand	IACS E10
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C) without derating IEC 60947-4-1
Ambient Air Temperature for Storage	-76...158 °F (-60...70 °C)
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Shocks15 Gn for 11 ms IEC 60068-2-7 Vibrations4 gn IEC 60068-2-6
Dielectric strength	1.89 kV 50 Hz IEC 60947-1
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1
Product Certifications	IEC UL CSA CCC EAC DNV-GL RMRS EU-RO MR LROS (Lloyds register of shipping) UKCA

Ordering and shipping details

Category	US10I1222347
Discount Schedule	0I12
GTIN	3389119215589
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Nbr. of units in pkg.	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	4.33 in (11.0 cm)
Package 1 Length	5.51 in (14.0 cm)
Package weight(Lbs)	14.7 oz (416.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	13
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	12.469 lb(US) (5.656 kg)

Contractual warranty

Warranty	18 months
-----------------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO₂ eq, Total Life cycle) 4

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Compliant

REACH Regulation [REACH Declaration](#)

California proposition 65 WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](#)

Use Again

Repack and remanufacture

Circularity Profile [End of Life Information](#)

Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Technical Illustration

Assembly's dimensions

