

Product data sheet

Specifications



braking resistor, Altivar, 60Ohms, 2.9kW, IP20

VW3A7751

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Compatibility	Altivar Machine ATV340 Altivar Process ATV900
Product or Component Type	Braking resistor
Ohmic value	60 Ohm
[Ue] rated operational voltage	24 V DC 250 V AC

Complementary

Product compatibility	Variable speed drive ATV930 wall mount 5.5 kW 380...480 V severe cycle Variable speed drive ATV930 wall mount 7.5 kW 380...480 V severe cycle Variable speed drive ATV930 wall mount 2.2 kW 200...240 V severe cycle Variable speed drive ATV950 wall mount 5.5 kW 380...480 V severe cycle Variable speed drive ATV950 wall mount 7.5 kW 380...480 V severe cycle Variable speed drive ATV340 4 kW 380...480 V severe cycle Variable speed drive ATV340 5.5 kW 380...480 V severe cycle Variable speed drive ATV930 7.5 kW 500...690 V severe cycle Variable speed drive ATV930 11 kW 500...690 V severe cycle Variable speed drive ATV930 10 hp 600 V severe cycle Variable speed drive ATV930 15 hp 600 V severe cycle
Duty cycle	Severe cycle (heavy duty) <54 s braking with 100 % braking torque for a 120 s cycle Severe cycle (heavy duty) <6 s braking with 165 % braking torque for a 120 s cycle
Average power available	2.9 kW 122 °F (50 °C)
Electrical connection	terminal <= 10 mm ² / AWG 8 drive terminal <= 2.5 mm ² / AWG 12 temperature control switch
Protection type	Thermal protection via drive or temperature control switch 120 °C
Width	15.4 in (390 mm)
Height	22.4 in (570 mm)
Depth	7.09 in (180 mm)
Product Weight	18.3 lb(US) (8.3 kg)

Environment

IP Degree of Protection	IP20
Ambient Air Temperature for Storage	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Operation	32...122 °F (0...50 °C)

Ordering and shipping details

Category	US1CP4E22209
Discount Schedule	CP4E

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

GTIN	3606480802430
Returnability	Yes
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	10.24 in (26.000 cm)
Package 1 Width	22.83 in (58.000 cm)
Package 1 Length	15.75 in (40.000 cm)
Package weight(Lbs)	20.457 lb(US) (9.279 kg)
Unit Type of Package 2	P06
Number of Units in Package 2	4
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	23.62 in (60.000 cm)
Package 2 Length	31.50 in (80.000 cm)
Package 2 Weight	100.566 lb(US) (45.616 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again


Repack and remanufacture

Take-back	No
-----------	----

Dimensions Drawings

Dimensions

Right Side and Front View



Dimensions in mm

A	B	C	A1	C1	Ø
390	180	570	370	380	6.6 x 9

Dimensions in in.


A	B	C	A1	C1	Ø
15.35	7.09	22.44	14.57	14.96	0.26 x 0.35

Mounting and Clearance


Mounting and Clearance

(1) Braking resistor

mm
in.




Connections and Schema

Recommended Schema**1 Braking Resistor**

A1 : Drive or external braking unit

A2 : Braking resistor

PA, PB : Bus DC

2 Braking Resistors

A1 : Drive or external braking unit

A2 : Braking resistor

PA, PB : Bus DC