



Overview

| | |
|--------------|----------------------------------------------------------------|
| Presentation | Basic Rack PDU 14.4 kW solution for high density installations |
| Lead time | Usually in Stock |

Main

| | |
|---------------------|------------------------------------------------------------------------------------------------------------------------|
| Main Input Voltage | 3 phase |
| Main Output Voltage | 208 V 3 phase |
| Number of rack unit | 0U |
| Cable length | 3 ft (0.91 m) |
| Number of cables | 1 |
| Provided Equipment | Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets Toolless Mounting Kit |

Physical

| | |
|---------------------|------------------------|
| Color | Black |
| Height | 70.00 in (177.8 cm) |
| Width | 2.20 in (5.6 cm) |
| Depth | 3.74 in (9.5 cm) |
| Net Weight | 16.14 lb(US) (7.32 kg) |
| Mounting Location | Side |
| Mounting preference | No preference |
| Mounting Mode | Rack-mounted |

Input

| | |
|----------------------------|----------|
| Line Rated Current | 40 A |
| Input current limits | 50 A |
| Load Capacity | 14400 VA |
| Input Frequency | 50/60 Hz |
| Number of input connectors | 1 CS8365 |

Output

| | |
|--------------------------------|------------------------------------------------------|
| Number of power socket outlets | 2 NEMA L6-30R 24 IEC 60320 C13 4 IEC 60320 C19 |
|--------------------------------|------------------------------------------------------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

| | |
|------------------------|----------------------------------------------|
| Product Certifications | CUL Listed CSA METI Denan UL Listed |
| Standards | UL 60950 |

Environmental

| | |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 23...113 °F (-5...45 °C) |
| Relative Humidity | 5...95 % |
| Operating altitude | 0...10000 ft |
| Ambient Air Temperature for Storage | -13...149 °F (-25...65 °C) |
| Storage Relative Humidity | 5...95 % |
| Storage altitude | 0...50000 ft (0.00...15240.00 m) |

Ordering and shipping details

| | |
|---------------------|-------------------------|
| GTIN | 731304240754 |
| Package weight(Lbs) | 24.87 lb(US) (11.28 kg) |

Packing Units

| | |
|------------------|---------------------|
| Package 1 Height | 80.98 in (205.7 cm) |
| Package 1 width | 3.11 in (7.9 cm) |
| Package 1 Length | 12.24 in (31.1 cm) |

Offer Sustainability

| | |
|-----------------------------|-----------------------------------------------|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Lead free | Yes |
| Optimized Energy Efficiency | Energy efficient product |
| Take-back | Take-back program available |

Contractual warranty

| | |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|